

BATTERY D TYPE



Technical Reference

Specifications

Capacity	600mAh
Chemistry	NiCd
Dimensions	44 x 15 x 50mm
Nominal Voltage	3.6V
Number of Cells	3
Size	D

NiCd batteries for cordless telephones

Rechargeable NiCd batteries in heatshrink sleeving.

The list indicates the battery type for each telephone model.

Types B, L and M feature a connector (types B₁ and B₂ are identical, only the location and length of the cord differ).

Brand	Device	Type
Philips	TD 92//50	C
Matra	LATITUDE	B ₁
	AMARYS 150	B ₂
	AMARYS 250	
Telic Alcatel	T 290	A
Panasonic	KXT series: 3821, 3830, 3831, 800, VA 7020	D
	KXT series: 3815, 3824...3845	
Sony	SSP 100, 200, 300	D
Uniden	EX series (30 models)	D
Cobra	CP series	D
All American, Japanese and Korean models		D-F

ref.		release	Capacity	dimensions
Saft	housing	(V)	(mAh)	(mm)
784 443	A	4.8	600	29 x 50 x 29
784 444	B ₁	3.6	600	43 x 51 x 17
783 329	B ₂	3.6	600	43 x 51 x 17
784 445	C	4.8	600	57 x 50 x 15
784 130	D	3.6	600	44 x 50 x 15
784 115	F	4.8	600	57 x 50 x 15