


Splintentreiber • Parallel Pin Punches



Splintentreiber • Parallel Pin Punches					
Art. No. poliert/polished	-L- mm	○ mm	∅ mm	⚖ g	
450 002 0	150	10	2	65	10
450 025 0	150	10	2,5	65	10
450 003 0	150	10	3	70	10
450 035 0	150	10	3,5	70	10
450 004 0	150	10	4	70	10
450 045 0	150	10	4,5	70	10
450 005 0	150	10	5	75	10
450 006 0	150	10	6	80	10
450 007 0	150	12	7	110	10
450 008 0	150	12	8	115	10
450 009 0	150	12	9	120	10
450 010 0	150	12	10	125	10
451 010 0	150	14	10	130	10
451 012 0	150	14	12	135	10
451 014 0	150	16	14	175	10
451 104 0	175	10	4	80	10
451 105 0	175	10	5	90	10
451 106 0	175	10	6	95	10
451 108 0	175	12	8	110	10
451 110 0	175	12	10	120	10



DIN 6450



Splintentreibersatz • Set of Parallel Pin Punches



Art. No. 425 170 0
Kunststoffhalter
Plastic Stand



Art. No. 425 150 0
Kunststoffkassette
Plastic Case



Art. No. 425 160 0
Metallkassette
Metal Case

Splintentreibersatz • Set of Parallel Pin Punches		
	Artikel	Art.No.
1	Splintentreiber Parallel Pin Punch	450 003 0
1	Splintentreiber Parallel Pin Punch	450 004 0
1	Splintentreiber Parallel Pin Punch	450 005 0
1	Splintentreiber Parallel Pin Punch	450 006 0
1	Splintentreiber Parallel Pin Punch	450 008 0
1	Splintentreiber Parallel Pin Punch	450 010 0