

GDME GB1 LG 230

Industrial Connectors: Rectangular connectors GDM-series: Type AEN 175301-803 (DIN 43650) / ISO 4400: Electronic inserts for GDME

Product description

Description bridge-type rectifier with protective circuit (varistor) and function indicator (glow lamp)

Type GDME GB1 LG 230

Order No. 831 834-001

Standard DIN EN 175 301-803-A

Construction type A


Description of Wiring

LED color glow lamp

Voltage rectifier bridge-type rectifier

Suppressor varistor

Drawing



Technical data

Rated voltage AC/DC 250 V

Rated current 2 A (SEV 1011 : 1.5 A) AC / 1 A DC

Environmental conditions

Temperature range -40 °C to +110 °C

Packing unit

Packaging unit 50 pieces