




THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		LOC	DIST	REVISIONS					
© COPYRIGHT - By -		ALL RIGHTS RESERVED.		-	-	P	LTR	DESCRIPTION	DATE	DWN	APVD
							G2	NEW DRAWING PER ECO-11-019045	03APR12	KH	DR

AMP WIRE RANGE	Listed FILE E13288	LR7189 Certified
22-16 AWG SOLID OR STRANDED	22-16 AWG SOLID OR STRANDED	22-16 AWG SOLID OR STRANDED

100	LOOSE PC, BOX	8-328394-1
5000	ON TAPE REEL	2-328394-1
1000	LOOSE PIECE	328394
QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN KIRAN HOLAL 03APR12	TE Connectivity					
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	RECOMMENDED OPERATING TEMPERATURE: 105°C [221°F]		DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK ROHDE DANIEL 03APR12	NAME WIRE TERMINAL P.I.D.G-SPADE WIRE SIZE: 22-16				
		VOLTAGE RATING: 300V MAX			0 PLC ± - 1 PLC ± - 2 PLC ± 0.20[.008] 3 PLC ± - 4 PLC ± - ANGLES ± 5°	APVD ROHDE DANIEL 03APR12					
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	WIRE CROSS SECTIONAL AREA RANGE: 0.26-1.65mm² [509-3260] CIR.MIL SOLID OR STRANDED		MATERIAL 	FINISH 	PRODUCT SPEC -	SIZE A3			CAGE CODE 00779	DRAWING NO C-328394
FOR ORDER ENTRY	1-800-526-5142					APPLICATION SPEC -	RESTRICTED TO -			WEIGHT -	
CUSTOMER DRAWING							SCALE 10:1	SHEET 1 OF 1	REV G2		