


LOC	DIST	REVISIONS				
P	LTR	DESCRIPTION		DATE	DWN	APVD
	P1	REVISED PER ECO-11-004820		11MAR11	RK	HMR

AMP WIRE RANGE	 Listed	 LR7189 Certified
16-14 AWG SOLID OR STRANDED	16-14 AWG SOLID OR STRANDED	16-14 AWG SOLID OR STRANDED



- 1

STAMP AMP 16-14* APPROX AS SHOWN
- 2

WIRE INSULATION DIA: 3.00-4.90 [.118-.193]
- 3

TONGUE MATERIAL THK: 0.79^{±0.05} [.031^{±.002}]
- 4

MATERIAL: BODY - CU PER ASTM B152
SLEEVE - PVC, COLOR - BLUE
- 5

MATERIAL: BODY - CU PER ASTM B152
SLEEVE - PVC, COLOR - BLACK
- 6

REPLACED BY 34163

OBSOLETE

6

OBSOLETE

OBSOLETE	25	LOOSE PIECE, BAG		8-34163-5
	100	LOOSE PIECE, BOX		8-34163-1
		LOOSE PIECE		2-34163-2
	4000	ON TAPE, REEL		2-34163-1
	-	LOOSE PIECE		34163
	QTY	PACKAGE TYPE	PART NO.	

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 105°C [221° F]		THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN DK SCHRUM 08/06/92		 TE Connectivity					
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: N/A		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.20[.008] 3 PLC ± - 4 PLC ± - ANGLES ± -	CHK RE HERSEY 11/10/92	APVD M ELLIS 11/10/92	NAME TERMINAL, RING TONGUE, PLASTI-GRIP WIRE SIZE: 16-14 AWG							
	TOOLING ASSISTANCE CENTER 1-800-722-1111														
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111		CIRCULAR MIL AREA: 1.04-2.62mm² [2,050-5,180] SOLID OR STRANDED			MATERIAL SEE NOTES	FINISH TIN PER ASTM B545	PRODUCT SPEC 108-1034		APPLICATION SPEC NOT AVAILABLE		SIZE A3	CAGE CODE 00779	DRAWING NO C-34163	RESTRICTED TO -
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.						WEIGHT -			CUSTOMER DRAWING				
											SCALE 4:1		SHEET 1 OF 1		REV P1