


---

Item no.: 773-173  
Product description: Push-wire connector for junction boxes 3-conductor terminal blocks cover in red

---



Produkt kann von Bild abweichen / product may differ

Packing unit 500 10\*50 pieces

RoHS compliant

|                                  |                         |
|----------------------------------|-------------------------|
| Product group                    | 7 (Push Wire Conn.)     |
| pole count                       | 3                       |
| Cross section [mm <sup>2</sup> ] | 2.5 - 6 mm <sup>2</sup> |
| Cross section [AWG]              | 14 - 10 AWG             |
| Connection method                | PUSH WIRE <sup>®</sup>  |
| Measured voltage EN              | 400 V                   |
| Measured shock voltage           | 4 kV                    |
| Pollution degree                 | 2                       |
| Current intensity EN             | 41 A                    |
| Weight                           | 5.73 g                  |
| Color                            | transparent             |
| Wiring type                      | Side-entry              |
| No. of connection Points         | 3                       |
| No. of potentials                | 1                       |
| Height                           | 14.2 mm                 |
| Height                           | 0.559 in                |
| Width                            | 25.6 mm                 |
| Width                            | 1.008 in                |
| Depth                            | 20.1 mm                 |

|                   |          |
|-------------------|----------|
| Depth             | 0.791 in |
| Strip length from | 12 mm    |
| Strip length to   | 13 mm    |
| Strip length      | 0.49 in  |



| Item number | Admission office | Approval no.       | Voltage [V] | Current [A] | Cross section [ mm² ] |
|-------------|------------------|--------------------|-------------|-------------|-----------------------|
| 773-173     | CSA              | 154112-1059435     | 600         | 30          | 14-10                 |
| 773-173     | ENEC15           | DK137981-01        | 400         | 41          | 2,5-4                 |
| 773-173     | ENEC15           | DK140612-01        | 400         | 41          | 2,5-6                 |
| 773-173     | PSE              | JET0695-43040-1001 | 600         | 30          | 14-10sol/str          |
| 773-173     | RosTest          | AB24 B04007        |             |             |                       |
| 773-173     | UL listed        | E69654             | 600         | 20          | 14-10sol/str          |

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected