

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [03-12-2121](#)
Status: **Active**
Description: 3.18mm Diameter, HCS125 Pin and Socket Plug Housing, 12 Circuits, 3 Row, with Panel Mount Ears

Documents:

[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Drawing \(PDF\)](#)

Agency Certification

UL E29179

General

Product Family Crimp Housings
Series [2201](#)
Application Power, Wire-to-Wire
Product Name HCS-125
UPC 800754942577

Physical


Circuits (maximum) 12
Color - Resin Natural
Flammability 94V-2
Gender Dual
Glow-Wire Compliant No
Material - Resin Nylon
Net Weight 5.945/g
Number of Rows 3
Packaging Type Bag
Panel Mount Yes
Pitch - Mating Interface 6.60mm
Stackable No
Temperature Range - Operating -40°C to +105°C

Material Info

Old Part Number 2201-P

Reference - Drawing Numbers

Sales Drawing SD-2201-*



Series

image - Reference only

EU RoHS

**ELV and RoHS
Compliant**
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Not Reviewed

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

[2201Series](#)

Mates With

[2201r](#)

Use With

[8947](#) , [1900](#) male crimp terminals, [1901](#) ,
[2046](#) , [2047](#) , [42546](#) , [42547](#) , [42554](#) , [42555](#)
 , [8946](#)