



TRUNK CABLE P/N	OVERALL LENGTH, L (m)	CABLE TYPE	FIBER TYPE	CONNECTOR/ CABLE COLOR	INSERTION LOSS	RETURN LOSS				
1062250085	1.0 +0.2 / -0	SINGLE JACKET	MM 50/125 μm OM3 BIF	AQUA / AQUA	0.5 dB @ 850 nm	---				
1062250086	3.0 +0.2 / -0									
1062250087	5.0 +0.2 / -0									
1062250037	10.0 +0.2 / -0									
1062250088	15.0 +0.3 / -0									
1062250038	25.0 +0.5 / -0	RUGGEDIZED DUAL JACKET								
1062250039	50.0 +1.0 / -0									
1062250040	100.0 +2.0 / -0	SINGLE JACKET	MM 50/125 μm OM4 BIF							
1062250089	1.0 +0.2 / -0									
1062250090	3.0 +0.2 / -0									
1062250091	5.0 +0.2 / -0									
1062250041	10.0 +0.2 / -0									
1062250092	15.0 +0.3 / -0	RUGGEDIZED DUAL JACKET								
1062250042	25.0 +0.5 / -0									
1062250043	50.0 +1.0 / -0	SINGLE JACKET	SM 9/125 μm OS2 ITU-T G.657.A1 BIF	YELLOW / YELLOW	0.5 dB @ 1550 nm	- 50 dB @ 1550 nm				
1062250044	100.0 +2.0 / -0									
1062250093	1.0 +0.2 / -0									
1062250094	3.0 +0.2 / -0									
1062250095	5.0 +0.2 / -0									
1062250045	10.0 +0.2 / -0									
1062250096	15.0 +0.3 / -0	RUGGEDIZED DUAL JACKET								
1062250046	25.0 +0.5 / -0									
1062250047	50.0 +1.0 / -0									
1062250048	100.0 +2.0 / -0									

CONNECTIONS	
FROM	TO
P1-1 THRU P1-12	P2-13 THRU P2-24
P1-13 THRU P1-24	P2-1 THRU P2-12





NOTES:

- ENDCAPS ARE NOT SHOWN BUT INLCUED.
- LABEL IS PRINTED WITH MOLEX P/N AND SERIAL NUMBER.
- FOR DETAILED PRODUCT SPECIFICATION SEE DOCUMENT 1062250000 ES.
- CABLE CONSTRUCTION:
 - L < 25 meters - SINGLE JACKET CABLE
 - L ≥ 25 meters - RUGGEDIZED CENTRAL TUBE CABLE
- INSERTION LOSS TEST DATA IS PROVIDED WITH EACH SHIPMENT.
- PACKAGING:
 - L < 50 meters - INDIVIDUALLY COILED AND BAGGED
 - L ≥ 50 meters - SHIPPED ON SPOOLS



VIEW A
SCALE 5:1



VIEW B
SCALE 5:1

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																		
QUALITY SYMBOLS		2017/10/30		2017/11/08		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE		molex® MPO(F) TO MPO(F) TRUNK CABLE, FLEXIBEND BOOT, 24 FIBER, PLENUM						
= 0	EC NO: 167430 DRWN: IGUMIN CHKD: IGUMIN REV: B1	APPR: IGUMIN	ANGULAR TOL ± °		mm		1:1											
= 0			4 PLACES ±		IGUMIN		2017/03/13											
= 0			3 PLACES ±		CHK'D BY		DATE											
= 0			2 PLACES ±		CHKD BY		DATE											
= 0			1 PLACE ±		APPR BY		DATE											
= 0			0 PLACES ±		IGUMIN		2017/03/21											
= 0			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DRAWING SIZE		THIRD ANGLE PROJECTION		D				SERIES		MATERIAL NUMBER		CUSTOMER	
= 0											106225		SEE TABLE					
= 0											DOCUMENT NUMBER		DOC TYPE		DOC PART		SHEET NUMBER	
= 0											1062250037		PSD		000		1 OF 1	