

MICRO SWITCH

FREEPORT ILLINOIS, U.S.A
A DIVISION OF HONEYWELL

FED. MFG. CODE 91929

SWITCH — BASIC

CATALOG LISTING

BM-1RW842255511-A2

BM-1RW842255511-A2

M

DRAWING
NUMBER

7

ISSUE

8

RELEASE NO. PR-8150

REPLACES X69903-BM

CHECK

REVISIONS

ASD 23NOV07

CHECK

2 OCT 79


CEB 2 OCT 79

CHECK

CEB 2 OCT 79

CHECK

CEB 2 OCT 79




NOTE -

- △ - MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 MAX DIA ON $1.000 \pm .002$ CENTERS
- 2 - SEALED CONSTRUCTION PROVIDES SPLASH RESISTANCE.

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS

OPERATING FORCE ——— 2 OZ MAX

RELEASE FORCE ——— 1/4 OZ MIN

DIFFERENTIAL TRAVEL ——— .001 - .013

OVERTRAVEL ——— .094 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

22A 125, 250 OR 480 VAC
1/2 HP 125 VAC, 1 HP 250 VAC

L288
L315
L318



22A 250V ~ T85 5E4

SCALE FULL

DO NOT SCALE PRINT

TOLERANCES

APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE:

DIM.	TOL.	DIM.	TOL.
mm	mm/in	in	mm/in
NO PLACES	X	1/64	
ONE PLACE	X, X	0.010/0.015	X, X
TWO PLACES	X, XX	0.001/0.005	X, XX
THREE PLACES	X, XXX	0.0001/0.0005	X, XXX
ANGLES			

DESIGN UNITS ☐ SI METRIC

US CUSTOMARY ☒

WEIGHT .076 LB

RASTER

FO-52848-A

DRAWN

GJW 2 OCT 79

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[BM-1RW84225511-A2](#)