



MALE END VIEW






BOARD LAYOUT




TYPICAL PANEL CUTOUT





SPECIFICATIONS

CONTACT CARRIER MATERIAL	NYLON OR TPU
CONTACT MATERIAL/PLATING	BRASS/GOLD
HOUSING, LOCKNUT MATERIAL/PLATING	BRASS/NICKEL
O-RING MATERIAL	NITRILE
RATED CURRENT [A]	4.0 A
RATED VOLTAGE [V]	250 V
NUMBER OF CONDUCTORS [AWG]	5 PRINTED CIRCUIT PINS
TEMPERATURE RATING	-40°C to +105°C (-40°F to +221°F)
PROTECTION CLASS	MEETS NEMA 1,3,4,6P AND IEC IP68



PA6 PIN
SUPPORT
INCLUDED





END VIEW
LOCKNUT NOT SHOWN

SOURCE DRAWING - FOR REFERENCE ONLY

G DRAWING PROCESSED AS PART OF ECO 33971				CBM 04/07/11 33971				RELATED DOCUMENTS				3RD ANGLE PROJECTION		THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.		TURCK INC High Technology Sensors and Automation Controls 3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com									
								SEE SPECIFICATIONS				ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY		DRFT JBJ DATE 12/17/96						DESCRIPTION FSFD 4.5					
																						DSGN		SCALE 1=.8	
																						UNIT OF MEASUREMENT MILLIMETER [INCH]		IDENTIFICATION NO. U5118-51	
ECO NO.				CONTACT TURCK FOR MORE INFORMATION				DO NOT SCALE THIS DRAWING		FILE: U5118-51				SHEET 1 OF 1											