


Model 4538 Minigrabber® Test Clip To Stacking Banana Plug With Retractable (Coiled) Cord



FEATURES:

- Retractable cord to allow connections at various lengths.
- Banana Plug stackable vertically and cross stackable.
- Ideal for connecting test equipment to terminals or wire wrap posts.

MATERIALS:

Conn: 1st End - Minigrabber® Test Clip

Material: Contact – Beryllium Copper per QQ-C-533, Alloy 165.

Spring – Stainless steel, Alloy 302.

Finish: Contact – Gold plated per MIL-G-45204, Type I, Class 00.

Insulation: Glass filled nylon. Color matches color of wire.

Retractable Cord: 20 AWG, stranding 42 x 36 t.c., PVC insulated, 3.71 (.146) O.D.

Color: See Ordering Information

Conn: 2nd End – Standard Stacking Banana Plug

Material: Spring - Beryllium Copper per QQ-C-533, Alloy 172, cond. HT.

Plug Body - Brass per QQ-B-626, Alloy 360, ½ Hard.

Finish: Nickel plated per QQ-N-290, Class 2, 200/300 microinches.

Insulation: Polypropylene molded to plug body and wire. Color matches color of wire.

RATINGS:

Operating Temperature: +55°C. (+131°F.) Max.

Voltage: Hand-held testing: 30VAC/60VDC Max.

Hands free testing in controlled voltage environments: 300 WVDC Max.

Current: 5 Amperes

ORDERING INFORMATION: Model 4538-*

*= Color, -0 Black, -2 Red

Ordering Example: 4538-2 Color is Red

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA