




THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00		E	REVISED PER ECO-14-011808	09AUG2014	AP	SB



- CONNECTOR ACCEPTS SIZE 20 DF SOCKET CONTACTS, RETENTION TINES ARE AN INTEGRAL PART OF INSERT.
- CONNECTOR COMPLIES WITH 108-40005 WHERE APPLICABLE.
- GLASS-FILLED PBT OR GLASS-FILLED NYLON, UL94V-0 RATED. COLOR: BLACK
- STEEL PER ASTM A109.
- TIN OR TIN-LEAD PLATED PER MIL-T-10727.
- TIN PLATED PER MIL-T-10727 OVER COPPER PER MIL-C-14550.

OBSOLETE	SMALL PACK	6	.120	207463-4
OBSOLETE	STANDARD	5	.154	207463-2
	STANDARD	6	.120	207463-1

		PACKAGING TYPE		SHELL FINISH		A		PART NO									
THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN S.WELDON 7-19-85		TE TE Connectivity											
				CHK J.GERACE 7-29-85													
				APVD L.BREKOSKY 7-29-85													
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± 2°		NAME		RECEPTACLE CONNECTOR, SIZE 3, 25 POSITION, AMPLIMITE™ HDP											
				PRODUCT SPEC													
				APPLICATION SPEC													
				—													
						SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO					
MATERIAL MOLDED PARTS:		FINISH		WEIGHT —		A2		00779		C=207463		—					
SHELLS:		SHELLS: SEE TABLE		CUSTOMER DRAWING								SCALE 4:1		SHEET 1 of 1		REV E	

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.