




PR1 Series



Panel Cutout



Water Protection Option



PVC Cap (IP54)

FEATURES

- High Rating with UL and VDE Approvals
- Maintained and Momentary Option
- PVC Cap for Water and Dust Protection

SPECIFICATIONS:

RATING: *RATING OPTION C:*

16A 125VAC [UR, cUR]
3/4HP 250VAC [UR, cUR]
16(6)A 250V~ 1E4 T125 [VDE]
10(4)A 250V~ 5E4 T125 [VDE]

TEMPERATURE: -20°C to 105°C [UR, cUR]
-20°C to 125°C [VDE]

ELECTRICAL LIFE: 10,000 Cycles

CONTACT RESISTANCE: 35mΩ Max.

INSULATION RESISTANCE: 100MΩ Min. at 500VDC

DIELECTRIC STRENGTH: 1,500VAC for 1 Minute

INGRESS PROTECTION: IP54 with PVC Cap

MATERIALS:



Body: Polyamide 6/6, UL94 V-2

ACTUATOR: Polyamide 6/6, UL94 V-2


Polycarbonate, UL94 V-2

CONTACTS: Silver Alloy

TERMINALS: Silver Plated Brass



Illumination Option



Full



PR144C1200



PR144EC1100



PR144EC1000-116
ACC-F03-1

PR142C1000-116

Series	Terminal	Function	Rating	Body Color	Actuator Color	Marking Color	Marking Type	Lens Style	Lens Color	Lamp Voltage
PR1	4 - 6.3mm Tabs	1 Pole: 1 - Off-On 4 - Off-(On) 2 Pole: 2 - Off-On E - Off-(On)	C - 16A 125VAC	1 - Black 2 - White 3 - Almond 4 - Grey 9 - Red	0 - Full Illum. 1 - Black 2 - White 3 - Almond 4 - Grey 5 - Orange 7 - Blue 8 - Green 9 - Red	0 - None 1 - Black 2 - White 8 - Red	0 - None 1 - Power Symbol Vert. 3 - Reset Symbol Vert. 5 - POWER Vert. 7 - RESET Vert.	1 - Full	0 - Clear 1 - Red 2 - Amber 3 - Green 4 - Blue	3 - 6V 4 - 12V 5 - 24V 6 - 125V 7 - 250V

Accessories Series	Type	Options
ACC	F03	

PVC Cap and Frame:
F03

Colors for Frame:
1 - Black
2 - White

Custom Colors and Markings Available Upon Request

For Illuminated Switches Only

EXAMPLE PART NUMBERS:

PR141C1100 1P Off-On
Black Body/Actuator, No Marking

PR141C1900 1P Off-On
Black Body, Red Actuator, No Marking

PR144C1900 1P Off-(On)
Black Body, Red Actuator, No Marking



E-SWITCH®

www.e-switch.com

800.867.2717

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

E-Switch:

[PR142C1000-106/ACC-F03-1](#) [PR142C1000-107/ACC-F03-1](#) [PR142C1000-127](#) [PR142C1000-137](#) [PR142C1000-147](#) [PR14EC1000-114](#) [PR14EC1000-124](#) [PR14EC1000-134](#) [PR14EC1000-144](#) [PR14EC1000-116/ACC-F03-1](#) [PR14EC1000-136/ACC-F03-1](#) [PR142C3000-136](#) [PR142C1000-124](#) [PR141C1000-136](#) [PR141C1021-116](#) [PR142C1000-116](#) [PR141C1000-135](#) [PR144C1000-136](#) [PR141C1000-134](#) [PR142C1015-106](#) [PR144C1000-134](#) [PR14EC1000-137](#) [PR142C1000-117](#) [PR142C1011-107](#) [PR142C2000-137](#)