




UNIT: mm



PIN ASSIGNMENT:



Electrical test:
1. 100% short, open, miswire test
2. Conduct resistance: 2 Ohm(max)
3. Insulation resistance: 5Mohm(min)
4. dielectric test: DC 300V

⑥	PE BAG	1/10	CLEAR SIZE:230*300*0.05mm	PRINT BLACK	MADE IN CHINA	10PCS
⑤	PE BAG	1	CLEAR SIZE:100*200*0.05mm	PRINT BLACK	MADE IN CHINA	1PC
④	TIE	1	WHITE	L=100mm		
③	OUT JACKET	12g	BEIGE(V-29#)	PVC-40P (MOULD NO:WM-65)		
②	CABLE	1	BEIGE(V-29#)	USB2.0 UL2725 28#/1P+24#/2C+AEB OD:4.7mm L=1000±10MM		
①	CONN	2	USB2.0 B MALE NICKEL PIN G/F 3PCS TYPE INSULATOR COLOR:WHITE			
NO.	NAME	Q'TY	SPECIFICATION			

CNC Tech, LLC						
Industrial Cable and Connector Technology						
DRAWN	ZHONGHS	DRAWING NO				
CHECKED		CUSTOMER				
APPROVAL		ITEM NO.	102-1040-BE-00100			
DECIDED		DATE	2012-02-15			
VERSIONS/EDITION	A/0	PROJECTION				

CABLE BLACK PRINT
HI-SPEED USB Revision 2.0 SHIELDED 28AWG/1P+24AWG/2C
E189529 AWM STYLE 2725 80°C 30V VW-1 VEGA TECH

CNC Tech, LLC
Industrial Cable and Connector Technology