





Product Data Sheet

Part No. WT-2505 Washable Type

DIMENSIONS



φ 25 × H12.5

MAX. 1.0mm
12-BAND 100.0
FOLDING MATERIAL, PBI

Type	Unit	
Color		Black
Rated Voltage	(V)	6
Operating Voltage	(V)	3-7
Current Consumption	(mA)	MAX.80
Coil Resistance	(Ω)	27±4
Sound Output (Min)	(dB)	85
Resonance Frequency	(Hz)	730
Operating Temp	(C)	-20~+60
Storage Temp	(C)	-30~+70
Weight	(g)	10
Terminal		PIN TYPE
Dimension	mm	25 x H12.5
*applied voltage: Rated Voltage, 1/2 duty, square wave		
*distance for measurement 10cm		

FREQUENCY RESPONSE

