




NOTES:

1. ATTENUATION $\leq$ 0,30 dB, MEASURED AT 1300nm ACC. TO IEC 874-1
CLAUSE 4.4.7 METHOD 7 EQUILIBRIUM MODE CONDITION.
2. FILLED OUT TEST RESULT SHEET WILL BE SUPPLIED WITH EACH INDIVIDUALLY
PACKED ASSEMBLY.

- 3

BLANK LABEL.
- 4

CABLE LABEL INFO:
 - UNIQUE SERIAL NUMBER
 - TYCO LOGO PN
 - MANUFACTURING LOCN.

- 5

REEL LABEL INFO:
 - TYCO LOGO, MFG LOCATION
 - DESCRIPTION
 - TE CONNECTIVITY PART NUMBER, REV
 - BARCODE

- 6

NON CROSS OVER AS PER TABLE.
- 7

CABLE LENGTHS MORE THAN 40m WILL BE SUPPLIED ON REEL.
8. CABLE INFO:

CORE DIA - 62.5/125 μ m

OUTER DIAMETER - 2,5 x 5,0 mm

JACKET COLOR - ORANGE

JACKET MAYERIAL - LSZH

STANDARD LENGTHS ACCORDING TO CUSTOMER DRAWING 1206850	
PART NUMBER	"L" (meter)
X-5349580-Y	XY,0

1	-	FOPK BOX	-
1	-	FOPK REEL 7	-
1	-	FOAC REEL LABEL 5	-
2	-	DAT-85 LABEL	12
2	-	KIT, MM, CER, ASSY, BULK	11
2	-	ST CRIMP EYELET	10
1	-	ST BOOT RED	9
1	-	ST BOOT BLACK	8
4	-	DUST CAP, BLACK	7
1	-	SC DUPLEX HOUSING, BEAM HALF	6
1	-	SC DUPLEX HOUSING, RET. PLATE HALF	5
2	-	SC CERAMIC, OVERMOLDED	4
2	-	SC CRIMP EYELET	3
2	-	SC BOOT, BEIGE	2
L	-	FOCAB 62,5/125TZ 2.5S ORANGE	1
Qty	Part Number	Description	Item
THIS DRAWING IS A CONTROLLED DOCUMENT.			
DIMENSIONS: mm		DWN 12 SEP 05 CHK 12 SEP 05 APVD 12 SEP 05 PRODUCT SPEC APPLICATION SPEC MATERIAL - FINISH -	DWNGIRIYAPPA M DIWAKAR BELAVADI DIWAKAR BELAVADI TE Connectivity NAME FOMM62.5 LEAD 2,5S TZ SC - ST DPX SIZE A2 CAGE CODE 00779 DRAWING NO C=5349580 RESTRICTED TO -
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH		WEIGHT -	SCALE NTS SHEET 1 of 1 REV A1
CUSTOMER DRAWING			