




Terminal blocks

to Type 373

ASP051 page 47

Type 373

Header, centerline 2.5 mm / 0.098 inches, vertical mounting, square contact pins 0.8 mm / 0.031 inches, closed ends

Technical Data

V / A 150 / 5

130 V / 2.5 kV / 4 A

Insulation co-ordination according to IEC 664-1

Clearance and creepage distances min. 1.7 mm

Insulating material class CTI 600

Overvoltage category III III II

Pollution degree 3 2 2

Rated voltage 80 320 320

Rated test voltage 0.8 4 2.5

Protection category according to IEC 529

IP00

Solder pin dimension 0.8 x 0.8 mm

Recommended pc board hole dia.

Ø 1.3 mm


Solder pin length 3.2 mm

Pole size 2 - 12

Color green

Dimensions in mm

1 mm = 0.0394 in.



$L = (\text{pole size} - 1) \times \text{centerline} + 4.4 \text{ mm} / 0.173 \text{ inches}$

Part numbers (P/N)

(informations: page 111)

Type 373

centerline 2.5 mm / 0.098 inches

P/N 313731



Complete the part number by adding the pole size.

	02	03	04	05	06	07	08
09	10	11	12				

Standard pole sizes

Available on demand. Minimum order quantity 5000 pieces per item.