

Housing - HC-B 48-SML-100/M2PG29 - 1772201

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Box mounting base, with single locking latch, height 100 mm, with screw connection, 2x Pg29



Key commercial data

Packing unit	1 pc
GTIN	 4 017918 036874
Weight per Piece (excluding packing)	1327.0 GRM
Custom tariff number	85389099
Country of origin	Germany

Technical data

Dimensions

Height	100 mm
Width	120 mm
Length	145 mm
Wrench size, union nut	37 mm
External cable diameter	18 mm ... 27 mm (Cable 1)
	18 mm ... 27 mm (Cable 2)

Ambient conditions

Degree of protection of housing (IP)	IP65
Ambient temperature (operation)	-40 °C ... 125 °C

General

Note	For contact inserts HC-B48, DD216, M
Design	B48

Housing - HC-B 48-SML-100/M2PG29 - 1772201

Technical data

General

Housing type	Box mounting bases
Locking type	With single locking latch
No. of cable exits	2
Cable exit	Lateral
Screw connection	With
Type of the screw connection	2x Pg29
Housing material	Aluminum die-cast
Housing surface material	Powder-coated, gray
Seal material	NBR
Cable gland material	Nickel-plated brass
Cable seal material	NBR
Material lock	Stainless steel, handle: PA
Material grip body interlock	PA

Classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440209

ETIM

ETIM 2.0	EC000437
ETIM 3.0	EC000437
ETIM 4.0	EC000437
ETIM 5.0	EC000437

UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

Housing - HC-B 48-SML-100/M2PG29 - 1772201

Approvals

Approvals

Approvals

GOST

Ex Approvals

Approvals submitted

Approval details

GOST 

Drawings

Dimensioned drawing

