

> [PN Search](#)

YA252TC38

> Electrical Power
Interconnect division

FCI brings you more

✉ [Contact our sales/
technical support](#)✉ [Sample request](#)€ [Price request](#)📦 [Check distributor stock](#)📄 [Download](#)🔗 [Mating half](#)🔧 [Alternative parts](#)🔧 [Application tooling](#)

Not Applicable

Not Available

[Electrical Tooling](#)
[Installation Tooling](#)**Features Selected**

Region Canada
US

Wire Type Commercial Stranded Copper

Wire Size 1/0 AWG

Stud Hole Size 3/8 in.

Stud Hole Spacing 1 in.

Barrel Length Long Barrel

Tongue Angle Straight

Tongue Width 0.75 in.

Other Properties

Element A Index 12

UL Listed yes

CSA Certified yes

Strip Length 1-7/16 in.

[Home page](#)**Product quick search**

P/N Search

FCI Competitor

GORoHS/LF P/N
Search

Product type search

Alphabetical list

Connection type

Markets / Applications

[Product finder](#)[Literature](#)[Services](#)[Contact us](#)**Registered users**[Forgot password ?](#)[Register now](#)