



## Storage Rack for HIS-Boxes

### • HIS-Service Station

This sturdy Service Station contains up to 5 dispensers. It can be put on a bench or mounted to a wall. A special cutter is included and makes it easy to cut the tubing length as desired

Technical Table

| Article-No. | Description                                                                                                                                                                                            |
|-------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 365-30100   | <b>HIS-Service Station incl. cutter, contents:</b><br>5 dispensers HIS-3 (shrink ratio: 3:1), black, sizes are as follows: HIS-3/1, HIS-6/2, HIS-12/4 (2 pcs.), HIS-24/8                               |
| 365-20000   | <b>HIS-Service Station incl. cutter, contents:</b><br>5 dispensers HIS-Pack (shrink ratio: 2:1), black, sizes are as follows: HIS-1/8, HIS-3/16, HIS-1/4, HIS-3/8, HIS 1/2 and one RiteOn Starter Pack |
| 300-30000   | <b>HIS-Service Station incl. cutter, empty</b>                                                                                                                                                         |



HIS-Service Station contains 5 dispensers and a special cutter.

### • HIS-PACK

#### Features and Benefits

- E-beam Crosslinked Polyolefin, thin-wall and flexible
- Shrink ratio 2:1
- Available in colours: black, red, blue, transparent and yellow/green.
- 10 sizes from 1.2mm to 25.4mm
- Handy dispenser box including table with full range of applications

#### Application

- General purpose electrical insulation
- Protection against corrosion and mechanical abrasion



HIS-A.

Material Data

|                                     |                                        |
|-------------------------------------|----------------------------------------|
| Material                            | <b>Polyolefin, cross-linked (POX)</b>  |
| Shrink Ratio                        | <b>2:1</b>                             |
| Longitudinal change after shrinkage | <b>+/- 5%</b>                          |
| Minimum Shrink Temperature          | <b>+100 °C</b>                         |
| Operating Temperature               | <b>-55 °C to +125 °C</b>               |
| Insulation Class                    | <b>E (VDE 0530)</b>                    |
| Dielectric Strength                 | <b>20kV/mm according to ASTM D2671</b> |
| Flammability                        | <b>UL224 VW-1 (except clear)</b>       |



Please note! Not all products listed on this page may have this approval. For product specific approvals please refer to the Appendix.



## Heat Shrinkable Tubing 2:1 on a Reel

### • HIS-PACK

Technical Table

| Article-No. | Type               | Supplied<br>Ø D | Recov.<br>Ø d | Wall<br>(WT) | Pack Cont.<br>(m) | Colour              |
|-------------|--------------------|-----------------|---------------|--------------|-------------------|---------------------|
| 300-30120   | HIS-PACK-1.2/0.6   | 1.2             | 0.6           | 0.40         | 10                | Black (BK)          |
| 300-30122   | HIS-PACK-1.2/0.6   | 1.2             | 0.6           | 0.40         | 10                | Red (RD)            |
| 300-30123   | HIS-PACK-1.2/0.6   | 1.2             | 0.6           | 0.40         | 10                | Transparent (CL)    |
| 300-30126   | HIS-PACK-1.2/0.6   | 1.2             | 0.6           | 0.40         | 10                | Blue (BU)           |
| 300-30160   | HIS-PACK-1.6/0.8   | 1.6             | 0.8           | 0.40         | 10                | Black (BK)          |
| 300-30162   | HIS-PACK-1.6/0.8   | 1.6             | 0.8           | 0.40         | 10                | Red (RD)            |
| 300-30163   | HIS-PACK-1.6/0.8   | 1.6             | 0.8           | 0.40         | 10                | Transparent (CL)    |
| 300-30166   | HIS-PACK-1.6/0.8   | 1.6             | 0.8           | 0.40         | 10                | Blue (BU)           |
| 300-30240   | HIS-PACK-2.4/1.2   | 2.4             | 1.2           | 0.50         | 10                | Black (BK)          |
| 300-30242   | HIS-PACK-2.4/1.2   | 2.4             | 1.2           | 0.50         | 10                | Red (RD)            |
| 300-30243   | HIS-PACK-2.4/1.2   | 2.4             | 1.2           | 0.50         | 10                | Transparent (CL)    |
| 300-30246   | HIS-PACK-2.4/1.2   | 2.4             | 1.2           | 0.50         | 10                | Blue (BU)           |
| 300-30320   | HIS-PACK-3.2/1.6   | 3.2             | 1.6           | 0.50         | 10                | Black (BK)          |
| 300-30322   | HIS-PACK-3.2/1.6   | 3.2             | 1.6           | 0.50         | 10                | Red (RD)            |
| 300-30323   | HIS-PACK-3.2/1.6   | 3.2             | 1.6           | 0.50         | 10                | Transparent (CL)    |
| 300-30326   | HIS-PACK-3.2/1.6   | 3.2             | 1.6           | 0.50         | 10                | Blue (BU)           |
| 300-30327   | HIS-PACK-3.2/1.6   | 3.2             | 1.6           | 0.50         | 10                | Green-Yellow (GNYE) |
| 300-30480   | HIS-PACK-4.8/2.4   | 4.8             | 2.4           | 0.50         | 10                | Black (BK)          |
| 300-30482   | HIS-PACK-4.8/2.4   | 4.8             | 2.4           | 0.50         | 10                | Red (RD)            |
| 300-30483   | HIS-PACK-4.8/2.4   | 4.8             | 2.4           | 0.50         | 10                | Transparent (CL)    |
| 300-30486   | HIS-PACK-4.8/2.4   | 4.8             | 2.4           | 0.50         | 10                | Blue (BU)           |
| 300-30487   | HIS-PACK-4.8/2.4   | 4.8             | 2.4           | 0.50         | 10                | Green-Yellow (GNYE) |
| 300-30640   | HIS-PACK-6.4/3.2   | 6.4             | 3.2           | 0.60         | 5                 | Black (BK)          |
| 300-30642   | HIS-PACK-6.4/3.2   | 6.4             | 3.2           | 0.60         | 5                 | Red (RD)            |
| 300-30643   | HIS-PACK-6.4/3.2   | 6.4             | 3.2           | 0.60         | 5                 | Transparent (CL)    |
| 300-30646   | HIS-PACK-6.4/3.2   | 6.4             | 3.2           | 0.60         | 5                 | Blue (BU)           |
| 300-30647   | HIS-PACK-6.4/3.2   | 6.4             | 3.2           | 0.60         | 5                 | Green-Yellow (GNYE) |
| 300-30950   | HIS-PACK-9.5/4.7   | 9.5             | 4.7           | 0.60         | 5                 | Black (BK)          |
| 300-30952   | HIS-PACK-9.5/4.7   | 9.5             | 4.7           | 0.60         | 5                 | Red (RD)            |
| 300-30953   | HIS-PACK-9.5/4.7   | 9.5             | 4.7           | 0.60         | 5                 | Transparent (CL)    |
| 300-30956   | HIS-PACK-9.5/4.7   | 9.5             | 4.7           | 0.60         | 5                 | Blue (BU)           |
| 300-30957   | HIS-PACK-9.5/4.7   | 9.5             | 4.7           | 0.60         | 5                 | Green-Yellow (GNYE) |
| 300-31270   | HIS-PACK-12.7/6.4  | 12.7            | 6.4           | 0.60         | 5                 | Black (BK)          |
| 300-31272   | HIS-PACK-12.7/6.4  | 12.7            | 6.4           | 0.60         | 5                 | Red (RD)            |
| 300-31273   | HIS-PACK-12.7/6.4  | 12.7            | 6.4           | 0.60         | 5                 | Transparent (CL)    |
| 300-31276   | HIS-PACK-12.7/6.4  | 12.7            | 6.4           | 0.60         | 5                 | Blue (BU)           |
| 300-31277   | HIS-PACK-12.7/6.4  | 12.7            | 6.4           | 0.60         | 5                 | Green-Yellow (GNYE) |
| 300-31900   | HIS-PACK-19.1/9.5  | 19.1            | 9.5           | 0.80         | 5                 | Black (BK)          |
| 300-31902   | HIS-PACK-19.1/9.5  | 19.1            | 9.5           | 0.80         | 5                 | Red (RD)            |
| 300-31903   | HIS-PACK-19.1/9.5  | 19.1            | 9.5           | 0.80         | 5                 | Transparent (CL)    |
| 300-31906   | HIS-PACK-19.1/9.5  | 19.1            | 9.5           | 0.80         | 5                 | Blue (BU)           |
| 300-31907   | HIS-PACK-19.1/9.5  | 19.1            | 9.5           | 0.80         | 5                 | Green-Yellow (GNYE) |
| 300-32540   | HIS-PACK-25.4/12.7 | 25.4            | 12.7          | 0.90         | 5                 | Black (BK)          |
| 300-32542   | HIS-PACK-25.4/12.7 | 25.4            | 12.7          | 0.90         | 5                 | Red (RD)            |
| 300-32543   | HIS-PACK-25.4/12.7 | 25.4            | 12.7          | 0.90         | 5                 | Transparent (CL)    |
| 300-32546   | HIS-PACK-25.4/12.7 | 25.4            | 12.7          | 0.90         | 5                 | Blue (BU)           |
| 300-32547   | HIS-PACK-25.4/12.7 | 25.4            | 12.7          | 0.90         | 5                 | Green-Yellow (GNYE) |

All dimensions in mm. Subject to technical changes.