








PPF 1070E	Rated Current A	Leakage Current @ 250V 50Hz	Inductance		Connections		Approvals		
			L1 mH	L2 mH	Input	Output			
PPF 1070E-1/01	1	0.2mA	4.5	0.3	IEC 320	6.3 x 0.8 Faston	■	■	■
PPF 1070E-3/01	3	0.2mA	1.2	0.3	IEC 320	6.3 x 0.8 Faston	■	■	■
PPF 1070E-6/01	6	0.2mA	0.5	0.3	IEC 320	6.3 x 0.8 Faston	■	■	■
PPF 1070E-10/01	10	0.2mA	0.09	0.3	IEC 320	6.3 x 0.8 Faston	■	■	■



Temperature Range: -25°C to +85°C
Operating Voltage: 250Vac
Operating Frequency: 0 to 400Hz
Test Voltage: L+N to ground, 2700Vdc, 2 seconds

Varistor:
Zinc oxide type; energy absorption 21 Joules (current impulse defined in IEC 60-2 Section 6). Varistor voltage: 430Vdc(measured at 1mA); clamping voltage 710V at 10A

- Approved
- Submitted for Approval

DIMENSIONS

All dimensions are nominal and in mm



FRONT AND REAR MOUNTING

CIRCUIT DIAGRAM

