


FEMALE HEADER 2,00 mm

ID: 156


BL 12-43G

Series 501



TECHNICAL DATA

Pitch	2,00 mm
Insulating Material	high temp. thermoplast UL94V-0
Contact Material	phosphor bronze
Rated Current	1,5 Amp.
Rated Voltage	100 V _{RMS} /150 V _{DC}
Withstanding Voltage	min. 500 V _{RMS}
Operating Temperature	-40°C to +105°C
Maximum Soldering Temperature	260°C for 10 seconds



All dimensions in mm.
Other dimensions upon request.

	BL	12	-	43	G	XX	-	XX	U	
12:		1 row, pitch 2,00mm								U: RoHS-compliant with high temp. plastic
43:		mounting height 4,3mm								Poles: 3 - 40 contacts possible
G:		straight contacts								
Plating:	TT	= Sn								
	GG	= Au								