


ST04-16

OUTLINE DIMENSIONS



RATINGS

●Absolute Maximum Ratings


Item	Symbol	Conditions	Ratings	Unit
Storage Temperature	T _{stg}		-40~150	°C
Junction Temperature	T _j		150	°C
Peak Surge Reverse Current	I _{RSM}	10/1000 μ s, Non-repetitive	15	A
		10/200 μ s, Non-repetitive	28	
Maximum Reverse Voltage	V _{RM}		13.6	V

●Electrical Characteristics (Tl=25°C)

Item	Symbol	Conditions	Ratings	Unit
Breakdown Voltage	V _{BR}	I _R = 1mA	14.4~17.6	V
Clamping Voltage	V _{CL}	I _{PP} = 15A	MAX 23	V
Reverse Current	I _R	V _R = 13.6V	MAX 5	μ A


ST04-16

Clamping Voltage




ST04-16


Breakdown Voltage



ST04-16


Reverse Current





ST04-16

Junction Capacitance



ST04-16

Junction Capacitance

