

TM2ALM3LT

analog input/output module M238 - 2 inputs
thermocouple/temp low level- 1 output

Product availability: Stock - Normally stocked in distribution facility
Price*: 483.00 USD



Main

Commercial Status	Commercialised
Range of product	Modicon M238 logic controller
Product or component type	Input/Output analog module
Analogue input number	2
Input level	Low level
Analogue input type	Thermocouple 0...400 °C thermocouple T differential Thermocouple 0...1300 °C thermocouple K differential Thermocouple 0...1200 °C thermocouple J differential Temperature probe - 100...500 °C 3-wire Pt probe differential
Analogue output number	1
Analogue output type	Voltage 0...10 V Current 4...20 mA
Cross talk	<= 2 LSB

Complementary

Range compatibility	Advantys OTB Twido
Analogue input resolution	12 bits
Analogue output resolution	12 bits
LSB value	0.15 °C temperature probe 0.1 °C thermocouple 4.8 µA current current 2.5 mV voltage voltage
Input impedance	>= 1 MOhm
Load type	Resistive
Load impedance ohmic	>= 2000 Ohm voltage <= 300 Ohm current
Stabilisation time	20 ms
Conversion time	20 ms + 1 controller cycle time
Sampling duration	<= 60 ms thermocouple <= 20 ms temperature probe
Acquisition period	80 ms per channel + 1 controller cycle time 60 ms per channel + 1 controller cycle time thermocouple
Measurement error	0.2 % of full scale +/- 4 °C 0...400 °C thermocouple T 25 °C 0.2 % of full scale +/- 4 °C 0...1300 °C thermocouple K 25 °C 0.2 % of full scale +/- 4 °C 0...1200 °C thermocouple J 25 °C +/- 0.2 % of full scale 4...20 mA 4...20 mA 25 °C +/- 0.2 % of full scale 0...10 V 0...10 V 25 °C +/- 0.2 % of full scale - 100...500 °C 3-wire Pt probe 25 °C
Temperature coefficient	+/-0.015 %FS/°C 4...20 mA 4...20 mA +/-0.015 %FS/°C 0...10 V 0...10 V +/-0.006 %FS/°C 0...400 °C thermocouple T +/-0.006 %FS/°C 0...1300 °C thermocouple K +/-0.006 %FS/°C 0...1200 °C thermocouple J +/-0.006 %FS/°C - 100...500 °C 3-wire Pt probe
Repeat accuracy	+/-0.5 %FS input/output

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein. *Prices are indicative

Non-linearity	+/- 0.2 %FS voltage voltage +/- 0.2 %FS thermocouple +/- 0.2 %FS temperature probe +/- 0.2 %FS current current
Output error	+/- 1 %FS
Output ripple	<= 1 LSB
Total error	+/-1 %FS voltage voltage +/-1 %FS thermocouple +/-1 %FS temperature probe +/-1 %FS current current
Type of cable	Shielded cable
Insulation between channel and internal logic	Photocoupler
Supply	External supply
[Us] rated supply voltage	24 V DC
Supply voltage limits	19.2...30 V
Electrical connection	1 removable screw terminal block
Current consumption	50 mA 5 V DC internal 50 mA 24 V DC external
Product weight	0.19 lb(US) (0.085 kg)

Environment

Dielectric strength	500 V between the I/O and the external supply circuit 500 V between the I/O and internal logic 500 V between I/O channel
Width	0.93 in (23.5 mm)
Depth	2.76 in (70 mm)
Height	3.54 in (90 mm)

Ordering and shipping details

Category	22531 - PLCS, TWIDO, TWD
Discount Schedule	PC12
GTIN	00785901699231
Nbr. of units in pkg.	1
Package weight(Lbs)	0.44
Product availability	Stock - Normally stocked in distribution facility
Returnability	Y
Country of origin	JP

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS	Compliant - since 0830 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available Download Product Environmental

Contractual warranty

Period	18 months
--------	-----------