





REV.	DATE	DESCRIPTION
NC	06/30/05	INITIAL RELEASE
A	10/02/06	REMOVAL OF CRIMP NOTE 2



RECOMMENDED
CABLE STRIPPING DIM'S



NOTE:
1. CRIMPED FERRULE
HEX CRIMP SIZE .128"

8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex					
7						DRAWN	G.R.S.					10/02/06	
6						CHECKED			PART DESCRIPTION SMZ CRIMP JACK (FOR RG–1279/U, 187A/U)				
5						ISSUED							
4	FERRULE	COPPER	GOLD	1		SHEET	1 OF 1		PART NO. 142107				
3	CONTACT PIN	BRASS	GOLD	1									
2	INSULATOR	TEFLON	NATURAL	1				DWG. NO. 142107.DWG					
1	BODY	BRASS	GOLD	1	CAD FILE							REV.	A
	DESCRIPTION	MATERIAL	FINISH	QTY									