




Cable Types		
	RG213/U	RG214/U (Double Shield)
Model	1658-S-XX	1658-T-XX
Capacitance pf/ft	30.8	30.8
Nominal Impedance	50	50
Cable Diameter	Ø .405	Ø .425

MATERIALS:

Conn:1st end – Type “N” Male, See table above.

Finish: Body and Fitting, Tarnish resistant.

Center contact: Gold plated per requirement of MIL-C-39012.

Nominal Impedance: 50 Ohms.

Cable: See table above. Marking: "POMONA 1658-X-XX".

Conn:2nd end – Same as first end.

RATINGS:

Operating Voltage: 1000 VRMS Max.

Operating Temperature: +89°C Max.

ORDERING INFORMATION: Model 1658-X-XX

XX = Cable Lengths, Standard Length: 18" (457), 24" (610), 36" (914), 48" (1219) & 60" (1542).

Additional lengths can be quoted upon request.

Ordering Example: 1658-T-24 Indicates 24" in length

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ± .005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[1658-T-18](#) [1658-T-60](#) [1658-T-48](#) [1658-T-36](#) [1658-T-24](#)