


SWITCHES ROCKER

AC/DC HEAVY DUTY ROCKER SWITCHES




SPECIFICATIONS:

Current Rating:		15A @ 125V AC, 10A @ 250V AC 3/4 HP @ 125-250V AC			
Insulation Resistance:		100 Meg ohm (Min.)			
Dielectric Strength:		1000V (Min.)			
Base Material:		Phenolic			
Terminal Type:		.250" Quick Connect			
Part No.	Type	Action			Actuator
30-16600	SPST	ON	-	OFF	Black Nylon
30-16610	SPDT	ON	-	ON	Black Nylon
30-16620	SPDT	ON	OFF	ON	Black Nylon
30-16630	DPST	ON	-	OFF	Black Nylon
30-16660	DPST	(ON)	-	OFF	Black Nylon
30-16640	DPDT	ON	-	ON	Black Nylon
30-16680	DPDT	ON	-	(ON)	Black Nylon

Note: () = Momentary

HEAVY DUTY ROCKER SWITCHES




SPECIFICATIONS:

Current Rating:		20A @ 125V AC, 15A @ 250VAC, 125A Peak Inrush current			
Insulation Resistance:		100 Meg ohm (Min.)			
Dielectric Strength:		1000V (Min.)			
Base Material:		Nylon			
Terminal Type:		.250" Quick Connect			
Part No.	Type	Action			Actuator
30-16654	DPST	ON	-	OFF	Black Nylon
30-16625*	DPST	ON	-	OFF	Black Nylon w/on-off Legend

* 30-16625 = 3/4HP 125-250VAC

"V" STYLE ROCKER SWITCHES




SPECIFICATIONS:

Current Rating:		10A @ 125VAC, 5A @ 250 VAC, 1/2HP 125-250VAC			
Insulation Resistance:		100 Meg ohms (Min.)			
Dielectric Strength:		1000V (Min.)			
Base Material:		Nylon			
Terminal Type:		.250" Quick Connect			
Part No.	Type	Action			Actuator
30-370	SPST	ON	-	(OFF)	White Nylon
30-16751*	SPST	OFF	-	(ON)	White Nylon

Note: () = Momentary

* 30-16751 = 15A @ 125VAC, 10A @ 250VAC, 3/4HP 125-250VAC

SEALED LIGHTED ROCKER SWITCHES



SPECIFICATIONS:

Current Rating:		20A @ 12VDC			
Initial Contact Resistance:		10 Milli ohms (Max) @ 4VDC			
Insulation Resistance:		50 Meg ohms			
Dielectric Strength:		1500 Volts RMS			
Contact Material:		Silver CAD-Oxide, Silver Tin-Oxide, Fine Silver			
Terminal Material:		Brass or Copper/Silver Plate			
Terminal Type:		.250" Quick Connect			
Part No.	Type	Action			Actuator
30-16500	SPST	ON	-	OFF	Black with Amber Lens
30-16505	SPST	ON	-	OFF	Black with Green Lens
30-16510	SPST	ON	-	OFF	Black with Red Lens
30-16515	SPST	ON	-	OFF	Black with Blue Lens
30-16520	DPDT	ON	OFF	ON	Black with Amber Lens
30-16525	DPDT	ON	OFF	ON	Black with Green Lens
30-16530	DPDT	ON	OFF	ON	Black with Red Lens
30-16535	DPDT	ON	OFF	ON	Black with Blue Lens
30-16560	DPDT	(ON)	OFF	(ON)	Black with Amber Lens
30-16565	DPDT	(ON)	OFF	(ON)	Black with Green Lens
30-16570	DPDT	(ON)	OFF	(ON)	Black with Red Lens
30-16575	DPDT	(ON)	OFF	(ON)	Black with Blue Lens
30-16580*	SPST	ON	-	OFF	Black Nylon**
30-16585	DPDT	ON	-	ON	Black Nylon**
30-16590	DPDT	ON	OFF	ON	Black Nylon**

Note () = Momentary

* 30-16580 15A @ 125VAC, 10A @ 250VAC, 1/2HP 125-250VAC, UL/CSA

** =Non Lighted

Lamp is incandescent 12V Rated @ 10,000 Hrs.