

Communication Markets Division

3M™ Crimplok™+ Connector with Activation Tool and Protrusion-setting Cap

SC Singlemode and Multimode 250 µm/900 µm

3M™ Crimplok™+ Connectors provide fast, easy field termination of 250 and 900 µm singlemode and multimode fiber without a splice, gel or adhesive.

A metallic element within the connector mechanically locks the fiber in place. To install, the fiber is cleaved, inserted through the connector and locked in place using the 3M™ Crimplok™+ Activation Tool and round-shape protrusion-setting cap, which comes with every connector. The fiber tip is polished with the 3M™ Crimplok™+ Nano Finishing Tool. This hand tool utilizes a polishing film and an orbital mechanism that polishes with a single turn of the handle.

3M™ Crimplok™+ Connectors have a thermally balanced design that is tested for premises and FTTP applications for indoor and outdoor conditions.

The streamlined boot attached to the connector body minimizes the chance of losing or forgetting to install it during the termination process. After the installation, the boot keeps the fiber from kinking, even during side pull.



3M™ Crimplok™+ Connector SC Family

The Crimplok+ Connectors and Tools are RoHS compliant.*

Features	Benefits
No splice, gel or adhesive	No splice interface/potential optical loss point
Simple one-piece assembly tools	Fast, easy installation without electrical power
Angle nano finishing tool for SC/APC connectors	Helps eliminate high CapEx of angle cleaver
Polishing film/Protrusion-setting cap with every connector APC: Green lapping film / Translucent white cap UPC: White lapping film / Translucent blue cap	Always have new polishing film and appropriate protrusion-setting caps for respective APC and UPC connectors
One-piece, pre-assembled design	No small, loose parts
Field termination	Always the right cable length with virtually no cable slack to store
SC/APC angle polish	Low reflectance, <-60 dB for outdoor temperatures

3M™ Crimplok™+ Connector SC Specifications

	Multimode 6700-AT/62.5 (OM3/4)	Multimode 6700-AT/50 (OM2)	Multimode 6700-AT/50LOMMF (OM1)	Singlemode 8700-AT/UPC	Singlemode 8700-AT/APC
Insertion Loss (dB) typical	0.2	0.2	0.2	0.2	0.25
Reflectance (dB) typical at room temp	<-25	<-30	<-30	<-40	<-65
Reflectance (dB) max over operating temperature range	<-25	<-30	<-30	<-35	<-60
Operating temperature range (°C)	-10°C to 60°C	-10°C to 60°C	-10°C to 60°C	-40°C to 75°C	-40°C to 75°C
Storage temperature (°C)	-10°C to 60°C	-10°C to 60°C	-10°C to 60°C	-40°C to 85°C	-40°C to 85°C
Connector identification	beige/white	black/white	aqua/white	blue/white	green/white
Field termination kit	8765T-UPC	8765T-UPC	8765T-UPC	8765T-UPC	8765T-APC

Specifications Common to all 3M™ Crimplok™+ Connectors	
Material Connector ferrule Connector housing and body Boot	Zirconia ceramic Engineered resin Thermoplastic elastomer
Dimensions	8.1 × 9.0 × 45 mm (0.3" x 0.3" x 1.8")



3M™ Crimplok™+ Nano Finishing Tool SC/APC 8765-NF/APC



3M™ Crimplok™+ Connector Kit SC/APC 8765T-APC contains all the tools necessary for 3M™ Crimplok™+ Connector 8700-AT/APC



3M™ Crimplok™+ Activation Tool with
a 3M™ Crimplok™+ SC/APC connector

3M™ Crimplok™+ Connectors SC/UPC and
SC/APC with Protrusion-setting Caps

3M™ Crimplok™+ Connector Ordering Information

Product Number	Product Descriptions	Packaging	3M ID
8700-AT/APC	3M™ Crimplok™+ Connector SC/APC SM 250/900 µm with Activation Tool	60 connector/ pack	80611622004
8700-AT/UPC	3M™ Crimplok™+ Connector SC/UPC SM 250/900 µm with Activation Tool	60 connector/ pack	80611622087
6700-AT/62.5	3M™ Crimplok™+ Connector SC MM 62.5 µm, (OM1) with Activation Tool	60 connector/ pack	80611622111
6700-AT/50	63M™ Crimplok™+ Connector SC MM 50 µm, (OM2) with Activation Tool	60 connector/ pack	80611622095
6700-AT/50LOMMF	3M™ Crimplok™+ Connector SC MM 50 µm, (OM3/4) with Activation Tool	60 connector/ pack	80611622103
8765-AT/APC	3M™ Crimplok™+ SC/APC Activation Tool	1 tool/pack	80611621907
8765-AT/UPC	3M™ Crimplok™+ SC/UPC Activation Tool	1 tool/pack	80611621998
8765T-APC	3M™ Crimplok™+ SC/APC Connector Installation Kit	1 kit/pack	80611622145
8765T-UPC	3M™ Crimplok™+ SC/UPC Connector Installation Kit	1 kit/pack	80611622459
8700-AT/APC/C	3M™ Crimplok™+ Connector SC/APC SM 250/900 µm with Activation Tool, Easy Cleaver	120 connector/ pack	80611622335
8700-AT/UPC/C	3M™ Crimplok™+ Connector SC/UPC SM 250/900 µm with Activation Tool, Easy Cleaver	120 connector/ pack	80611622343
6700-AT/62.5/C-60	3M™ Crimplok™+ Connector SC MM 62.5 µm, (OM1) with Activation Tool, Easy Cleaver	60 connector/ pack	80611622418
6700-AT/50/C-60	3M™ Crimplok™+ Connector SC MM 50 µm, (OM2) with Activation Tool, Easy Cleaver	60 connector/ pack	80611622400
6700-AT/50LOMMF/C-60	3M™ Crimplok™+ Connector SC MM 50 µm, (OM3/4) with Activation Tool, Easy Cleaver	60 connector/ pack	80611622426

**RoHS 2011/65/EU" means that the product or part does not contain any of the substances in excess of the maximum concentration values ("MCVs") in EU RoHS Directive 2011/65/EU. The MCVs are by weight in homogeneous materials. This information represents 3M's knowledge and belief, which may be based in whole or in part on information provided by third party suppliers to 3M.

3M and Crimplok are trademarks of 3M Company.

Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

Warranty; Limited Remedy; Limited Liability.

This product will be free from defects in material and manufacture for a period of 12 months from the time of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. Except where prohibited by law, 3M will not be liable for any loss or damage arising from this 3M product, whether direct, indirect, special, incidental or consequential regardless of the legal theory asserted.



Communication Markets Division

6801 River Place Blvd.
Austin, TX 78726-9000 USA

Phone 1-800-426-8688
Fax 1-800-626-0329
Web 3M.com/Telecom

Please recycle. Printed in USA © 3M 2017.
All rights reserved. 80-6114-9880-1