


C-180398	Adatto p. applicatore standard		Adatto per Amp-O-Mator		
	N° Part.	Materiale	N° Part.	Materiale	
	180398-1	Ottone.	280085-1	Ottone.	OBSOLETE
	180398-2	Ottone stagnato.	280085-2	Ottone stagnato.	
	180398-3	Ottone argentato. ▲			
	180398-4	Bronzo fosforoso. ▲	280085-3	BRONZO FOSFOROSO	OBSOLETE ▲1
	180398-5	Bronzo fosf. stagn.	280085-4	BRONZO FOSF STAG	
	180398-6	Bronzo fosf. argent. ▲	280085-5	Acciaio ½ Hard	OBSOLETE ▲1
	180398-7	Ottone argentato. ▲	280085-6	Acciaio ½ Hard Ni plati.	OBSOLETE
	180398-8	Bronzo fosf. argentato. ▲			



OBSOLETE ▲

▲ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING
PER D.RENAUD/D.SINISI

Adatto per linguetta di sp. 0,8



Sez. A-A



AB	Revised for ET00-0319-97	05/97
AA	Revised for ET00-0132-97	18/3/97
Z	Revised for ET00-0448-96	21/10/96

© 1973 BY AMP INCORPORATED. ALL RIGHTS
RESERVED. AMP PRODUCTS COVERED BY
PATENTS AND/OR PATENTS PENDING.

**CUSTOMER COPY
REFERENCE ONLY**

AB1	ECO-10-000445	KK	AEG	JAN10
J	Revised For ET00-0080-34	14 FEB '92		
H	Aggiunti PN come da ECN 13003	31 MAY '88		
G	INS. RANGE WAS 3-4,3 DIA	15 JAN '88		
F	Rivisto	21-12 '82		
E	Aggiunti PN come da ECN 1415	21-12 '82		
LTR	REVISION RECORD	DR	CHK	DATE

MATERIAL AND FINISH

Vedi tabella



AMP ITALIA
VIA CERV 15
COLLEGNO (TORIN)

CLASS **.250 Series**

TYPE **F.F.**

WIRE RANGE INSULATION
1-2,5 mm² 24-38 Dia.

TOLERANCE EXCEPT
AS NOTED
± 0,4 ± 1° 0'

SCALE
4:1

LOC.
I

NO
A

C-180398

"250" Series Flag Fastin-on Rec.

DIMENSIONS IN (mm) DO NOT SCALE PRINT

PRINT DIST
5

9-1-73
10-1-73