




Units: mm



NOTE:
1.小PE袋/大PE袋对应料号.包袋数量及时间印刷样式:

CnC Tech, LLC	Industrial Cable and Connector Technology	770-20011-00100	10PCS.	RoHS	529
					表示2009年(按首次产品生产)印刷
		印客人/原料号			印刷对应的袋数




2. 外箱两个侧唛ITEM NO后面各贴一个35*22mm ROHS标签。

Electrical test:
1. 100% short, open, miswire test
2. Conduct resistance: 5 Ohm(max)
3. Insulation resistance: 10Mohm(min)
4. dielectric test: DC 300V

⑧	TIE	2	BLACK L=80mm
⑦	PE BAG	1/10	CLEAR SIZE: 280*330*0.05mm PRINT BLACK"MADE IN CHINA"+"10PCS"
⑥	PE BAG	1	CLEAR SIZE: 130*230*0.05mm PRINT BLACK"MADE IN CHINA"+"1PC"
⑤	S/R	3.0g	BLACK PVC 40P (Mould NO.:SR-048)
④	IN JACKET	1.6g	CLEAR LD-PE (Mould NO.:NM-006)
	OUT JACKET	6.6g	PVC-40P RED(RD-35),(Mould NO.WM-009)
③	IN JACKET	1.6g	CLEAR LD-PE (Mould NO.:NM-006)
	OUT JACKET	6.6g	PVC-40P WHITE(W-100)(Mould NO.WM-009)
②	CABLE	1	NOUL 28#(10/0.10+28/0.10)*2F JACKET BLACK OD2.8*5.6mm
①	CONN	4	RCA PLUG MALE 梅花型 TYPE NI-PLATED INSULATOR COLOR:BROWN
NO.	NAME	QTY	SPECIFICATION

CNC Tech, LLC				
Industrial Cable and Connector Technology				
DRAWN BY	LICHENG	DARTING NO.	V6/LJ0-094-082-4	
CHECKED BY		CUSTOMER	CNC	
APPROVAL BY		ITEM NO.	770-20011-00100	
DECIDE BY		DATE	2012-12-28	
VERSIONS/EDITION	A/0	PROJECTION		

Units:mm



Electrical test:
1.100% short,open,miswire test
2.Conduct resistance:5 Ohm(max)
3.Insulation resistance:10Mohm(min)
4.dielectric test:DC 300V

⑧	TIE	2	BLACK L=80mm
⑦	PE BAG	1/10	CLEAR SIZE: 280*330*0.05mm PRINT BLACK"MADE IN CHINA"+"10PCS"
⑥	PE BAG	1	CLEAR SIZE: 130*230*0.05mm PRINT BLACK"MADE IN CHINA"+"1PC"
⑤	S/R	3.0g	BLACK PVC 40P (Mould NO.:SR-048)
④	IN JACKET	1.6g	CLEAR LD-PE (Mould NO.:NM-006)
	OUT JACKET	6.6g	PVC-40P RED(RD-35),(Mould NO.:WM-009)
③	IN JACKET	1.6g	CLEAR LD-PE (Mould NO.:NM-006)
	OUT JACKET	6.6g	PVC-40P WHITE(W-100)(Mould NO.:WM-009)
②	CABLE	1	NOUL 28#(10/0.10+28/0.10)*2F JACKET BLACK OD2.8*5.6mm
①	CONN	4	RCA PLUG MALE 梅花型 TYPE NI-PLATED INSULATOR COLOR:BROWN
NO.	NAME	QTY	SPECIFICATION




NOTE:
1.小PE袋大PE袋对应料号,包袋数量及时间印刷样式:
CnC Tech, LLC
Industrial Cable and Connector Technology
770-20011-00150
10PCS
529
印袋人"产品料号
印对应的数量
表示529099(每袋次"产品生产周刷印)

2.外箱两个侧面ITEM NO后面各贴一个35*22mm ROHS标签.

CnC Tech, LLC
Industrial Cable and Connector Technology

DRAWN BY	LICHENG	DRAWING NO.	V6/LJ0-094-082-B
CHECKED BY		CUSTOMER	CNC
APPROVAL BY		ITEM NO.	770-20011-00150
DECIDE BY		DATE	2012-12-28
VERSION/EDITION	A/0	PROJECTION	

Units:mm



- Electrical test:
- 1.100% short,open,miswire test
 - 2.Conduct resistance:5 Ohm(max)
 - 3.Insulation resistance:10Mohm(min)
 - 4.dielectric test:Dc 300V

⑧	TIE	2	BLACK L=80mm
⑦	PE BAG	1/10	CLEAR SIZE: 280*330*0.05mm PRINT BLACK"MADE IN CHINA"+"10PCS"
⑥	PE BAG	1	CLEAR SIZE: 130*230*0.05mm PRINT BLACK"MADE IN CHINA"+"1PC"
⑤	S/R	3.0g	BLACK PVC 40P (Mould NO.:SR-048)
④	IN JACKET	1.6g	CLEAR LD-PE (Mould NO.:NM-006)
	OUT JACKET	6.6g	PVC-40P RED(RD-35),(Mould NO.WM-009)
③	IN JACKET	1.6g	CLEAR LD-PE (Mould NO.:NM-006)
	OUT JACKET	6.6g	PVC-40P WHITE(W-100)(Mould NO.WM-009)
②	CABLE	1	NOUL 28#(10/0.10+28/0.10)*2F JACKET BLACK OD2.8*5.6mm
①	CONN	4	RCA PLUG MALE 梅花型 TYPE NI-PLATED INSULATOR COLOR:BROWN
NO.	NAME	QTY	SPECIFICATION

NOTE:

1.小PE袋/大PE袋对应料号,包袋数量及时间印刷样式:

CnC Tech, LLC

Industrial Cable and Connector Technology

770-20011-00200

10 PCS. — RoHS — 529 —

印袋人产品料号


印袋人产品数量

表示529/0994(按结构产品生产周期印)



2.外箱两个侧面ITEM NO后面各贴一个35*22mm ROHS标签。

CnC Tech, LLC				
Industrial Cable and Connector Technology				
DRAWN BY	LICHENG	DRAWING NO.	V6/LJ0-094-082-C	
CHECKED BY		CUSTOMER	CNC	
APPROVAL BY		ITEM NO.	770-20011-00200	
DECIDE BY		DATE	2012-12-28	
VERSIONS/EDITION	A/0	PROJECTION		

Units:mm



PIN ASSIGNMENT:



NOTE:

1.小PE袋/大PE袋对应料号.包袋数量及时间印刷样式:

CnC Tech, LLC
Industrial Cable and Connector Technology
770-20011-00250

10 PCS. _____ 印客人产品料号
RoHS _____ 印对应的标签数量
529 _____ 表示2009年(按首次产品生产周印)

2. 外箱两个侧唛ITEM NO后面各贴一个35*22mm ROHS标签。

Electrical test:
1. 100% short, open, miswire test
2. Conduct resistance: 5 Ohm(max)
3. Insulation resistance: 10Mohm(min)
4. dielectric test: DC 300V

⑧	TIE	2	BLACK L=80mm
⑦	PE BAG	1/10	CLEAR SIZE: 280*330*0.05mm PRINT BLACK"MADE IN CHINA"+"10PCS"
⑥	PE BAG	1	CLEAR SIZE: 130*230*0.05mm PRINT BLACK"MADE IN CHINA"+"1PC"
⑤	S/R	3.0g	BLACK PVC 40P (Mould NO.:SR-048)
④	IN JACKET	1.6g	CLEAR LD-PE (Mould NO.:NM-006)
	OUT JACKET	6.6g	PVC-40P RED(RD-35)(Mould NO.:WM-009)
③	IN JACKET	1.6g	CLEAR LD-PE (Mould NO.:NM-006)
	OUT JACKET	6.6g	PVC-40P WHITE(W-100)(Mould NO.:WM-009)
②	CABLE	1	NOUL 28#(10/0.10+28/0.10)*2F JACKET BLACK OD:2.5,6mm
①	CONN	4	RCA PLUG MALE 梅花型 TYPE NI-PLATED INSULATOR COLOR:BROWN
NO.	NAME	QTY	SPECIFICATION

CNC Tech, LLC

Industrial Cable and Connector Technology


DRAWN BY	LICHENG	DRAWING NO.	V6/LJQ-094-002-D
CHECKED BY		CUSTOMER	CNC
APPROVAL BY		ITEM NO.	770-20011-00250
DECIDE BY		DATE	2012-12-28
VERSIONS/EDITION	A/0	PROJECTION	

4



C

2

Units:mm



PIN ASSIGNMENT:



NOTE:

1.小PE袋/大PE袋对应料号.包袋数量及时间印刷样式:

CnC Tech, LLC
Industrial Cable and Connector Technology
770-20011-00250

10 PCS. _____ 印客人产品料号
RoHS _____ 印对应的标签数量
529 _____ 表示2009年(按首次产品生产周印)

2. 外箱两个侧唛ITEM NO后面各贴一个35*22mm ROHS标签。

Electrical test:
1. 100% short, open, miswire test
2. Conduct resistance: 5 Ohm(max)
3. Insulation resistance: 10Mohm(min)
4. dielectric test: DC 300V




⑧	TIE	2	BLACK L=80mm
⑦	PE BAG	1/10	CLEAR SIZE: 280*330*0.05mm PRINT BLACK"MADE IN CHINA"+"10PCS"
⑥	PE BAG	1	CLEAR SIZE: 130*230*0.05mm PRINT BLACK"MADE IN CHINA"+"1PC"
⑤	S/R	3.0g	BLACK PVC 40P (Mould NO.:SR-048)
④	IN JACKET	1.6g	CLEAR LD-PE (Mould NO.:NM-006)
	OUT JACKET	6.6g	PVC-40P RED(RD-35)(Mould NO.:WM-009)
③	IN JACKET	1.6g	CLEAR LD-PE (Mould NO.:NM-006)
	OUT JACKET	6.6g	PVC-40P WHITE(W-100)(Mould NO.:WM-009)
②	CABLE	1	NOUL 28#(10/0.10+28/0.10)*2F JACKET BLACK OD:2.5,6mm
①	CONN	4	RCA PLUG MALE 梅花型 TYPE NI-PLATED INSULATOR COLOR:BROWN
NO.	NAME	QTY	SPECIFICATION

CNC Tech, LLC

Industrial Cable and Connector Technology

DRAWN BY	LICHENG	DRAWING NO.	V6/LJQ-094-002-D
CHECKED BY		CUSTOMER	CNC
APPROVAL BY		ITEM NO.	770-20011-00250
DECIDE BY		DATE	2012-12-28
VERSIONS/EDITION	A/0	PROJECTION	

Units:mm



- Electrical test:
- 1.100% short,open,miswire test
 2. Conduct resistance:5 Ohm(max)
 3. Insulation resistance:10Mohm(min)
 4. dielectric test:DC 300V

⑧	TIE	2	BLACK L=80mm
⑦	PE BAG	1/10	CLEAR SIZE: 280*330*0.05mm PRINT BLACK"MADE IN CHINA"+"SPCS"
⑥	PE BAG	1	CLEAR SIZE: 150*280*0.05mm PRINT BLACK"MADE IN CHINA"+"IPC"
⑤	S/R	3.0g	BLACK PVC 40P (Mould NO.:SR-048)
④	IN JACKET	1.6g	CLEAR LD-PE (Mould NO.:NM-006)
③	OUT JACKET	6.6g	PVC-40P RED(RD-35),(Mould NO.:WM-009)
②	OUT JACKET	1.6g	CLEAR LD-PE (Mould NO.:NM-006)
①	CABLE	1	NOUL 28#(10/0.10+28/0.10)*2F JACKET BLACK OD2.8*5.6mm
NO.	CONN	4	RCA PLUG MALE 梅花型 TYPE NI-PLATED INSULATOR COLOR:BROWN
	NAME	QTY	SPECIFICATION

CnC Tech, LLC			
Industrial Cable and Connector Technology			
DRAWN BY	LICHENG	DRAWING NO.	V6/LJ0-094-082-E
CHECKED BY		CUSTOMER	CNC
APPROVAL BY		ITEM NO.	770-20011-00500
DECIDE BY		DATE	2012-12-28
VERSIONS/EDITEON	A/0	PROJECTION	

NOTE:
1.小PE袋/大PE袋对应料号,包袋数量及时间印刷样式:

CnC Tech, LLC		Industrial Cable and Connector Technology	
770-20011-00500		5 PCS.	
RoHS		529	

2. 外箱两个侧面ITEM NO后面各贴一个35*22mm ROHS标签。