

V-RC/TGUM 11/KVD 11/LBL 12

Order No.: 1000041



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1000041>

M23 socket, 12-pos., straight, freely configurable, with solder
connection, for external cable diameter of 8 mm ... 12 mm

Commercial data

EAN	4017918399832
Pack	1 pcs.
Customs tariff	85366990
Weight/Piece	0.1003 KG
Catalog page information	Page 128 (PC-2009)

Product notes

WEEE/RoHS-compliant since:
06/22/2006



[http://
www.download.phoenixcontact.com](http://www.download.phoenixcontact.com)
Please note that the data given
here has been taken from the
online catalog. For comprehensive
information and data, please refer
to the user documentation. The
General Terms and Conditions of
Use apply to Internet downloads.

Technical data

General data

Nominal voltage U_N	120 V
Max. operating voltage U_{max}	135 V
Number of positions	12
Degree of protection	IP65/67
Inflammability class acc. to UL 94	V0

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

Master cable data

Type of connection	M23 screw locking
External cable diameter min.	8 mm
External cable diameter max.	12 mm

Connection assignment

Slot/position = pin = conductor color	1 / 4 (A) = 1 = WH
	2 / 4 (A) = 2 = GN
	3 / 4 (A) = 3 = YE
	4 / 4 (A) = 4 = GY
	5 / 4 (A) = 5 = PK
	6 / 4 (A) = 6 = RD
	7 / 4 (A) = 7 = BK
	8 / 4 (A) = 8 = VT
	1-8 / 1 (+ 120 V) = 11 = BN
	1-8 / 3 (0 V) = 9+10 = BU
	1-8 / 5 (PE) = 12 = GN/YE


Accessories

Item	Designation	Description
General		
1665062	PLUSCON-RCS	Special pipe spanner, tool for mounting the M23 connector housing (with assembly), for coupling and sleeve housing

Diagrams/Drawings

Schematic diagram

Pin assignment M23 socket, 12-pos., female side view



Address

PHOENIX CONTACT Inc., USA
586 Fulling Mill Road
Middletown, PA 17057, USA
Phone (800) 888-7388
Fax (717) 944-1625
<http://www.phoenixcon.com>



© 2010 Phoenix Contact
Technical modifications reserved;