



T&B®

Liquidtight Flexible Cord & Cable Fittings T&B Catalog Number:

UPC Number:	2940NM
Status:	78621079746
Description:	Active

1 in. straight nylon Ranger liquidtight cord connector, cord range .310-.560

Features

- Extended range with superior strain relief.
- Reduced overall size, fits into tighter spaces.
- Gland nut designed to restrict cable bending.

Application

- Provide a means for passing a cord cable into an enclosure through a bulkhead
- Suitable for Ordinary, Wet or Dry locations.

General

Material	Nylon
Cord and Cable Types	S, SO, SV, ST, STD, SJ, SJO, SJT, SJTO, SVD

Dimension Information

Hub Size (inches)	1
Dimension A (inches)	1 13/32
Dimension B (inches)	2 11/32
Dimension C (inches)	25/32
Cord Range (inches)	.310-.560
Throat Diameter (inches)	0.98

Specifications

3dmodel	Available on Website
---------	----------------------

Packaging

T&B Inner Pack	10
Package in Units	100
T&B Sold in UOM	Each
T&B Weight Per UOM	8 lbs. per 100

Application Support

T&B Instruction Sheets	ta00927-tb2
Product Overview	Available on Website
Specifications	Available on Website
Portable Cord Selection Table	Available on Website

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications

File Nbr:
E 13938

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com