




| LOC | DIST | REVISIONS |     |                         |  |  |         |     |      |
|-----|------|-----------|-----|-------------------------|--|--|---------|-----|------|
|     |      | P         | LTR | DESCRIPTION             |  |  | DATE    | DWN | APVD |
| AD  | 00   |           | A   | REV PER EC 0512-0647-04 |  |  | 10MAY05 | JA  | SF   |

1. WIRE RANGE 22-26 AWG.
2. INSULATION RANGE 0.91-1.37 [.036-.054] DIA.
3. PREPLATED 0.00127 [.000050] MIN MATTE TIN IN ZONES I & II, 0.000762 [.000030] MIN GOLD OVER 0.000762 [.000030] MIN NICKEL INLAY IN ZONE III.
4. PHOSPHOR BRONZE.
5. ZONE I (OUTSIDE SURFACES).
6. ZONE II (INSIDE SURFACES).
7. ZONE III (INSIDE SURFACES).
8. MAXIMUM CUTOFF.



SECTION Y-Y



SECTION Z-Z

|                                                                                                   |  |                                                                                                                                                      |                                                                                   |  |
|---------------------------------------------------------------------------------------------------|--|------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                                            |  | DWN<br>J. ALCORTA - DOCK5<br>CHK<br>A. FRANTUM<br>APVD<br>S. FLICKINGER<br>PRODUCT SPEC<br>108-25031<br>APPLICATION SPEC<br>114-25021<br>WEIGHT<br>- | tyco<br>Electronics<br>Tyco Electronics Corporation<br>Harrisburg, PA 17105-3608  |  |
| DIMENSIONS:<br>mm [INCHES]                                                                        |  | 10MAY05<br>10MAY05<br>10MAY05                                                                                                                        | NAME<br>CONTACT, RECEPTACLE,<br>HIGH PRESSURE,<br>MINI-TANDEM SPRING              |  |
|              |  | 0 PLC ± -<br>1 PLC ± -<br>2 PLC ± -<br>3 PLC ± 0.13[.005]<br>4 PLC ± -<br>ANGLES ± 1°<br>FINISH                                                      | SIZE<br>A2<br>CAGE CODE<br>00779<br>DRAWING NO<br>C-5531224<br>RESTRICTED TO<br>- |  |
| MATERIAL<br> |  | CUSTOMER DRAWING                                                                                                                                     | SCALE<br>4:1<br>SHEET<br>1 OF 1<br>REV<br>A                                       |  |