

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300240267](#)
Status: **Active**
Overview: [Brad Mini-Change Connectors](#)
Description: Mini-Change Single-Ended Cordset, 5 Poles, Male (Straight) to Pigtail, 15/18 AWG, DeviceNet Thick Flex-Rated Cable, 3.0m (9.84') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837

General

Product Family Industrial Cordsets
Series [130024](#)
Connector End A Mini-Change
Connector End B Pigtail
IP Rating IP67
Material - Contact Brass
Overview [Brad Mini-Change Connectors](#)
Product Name DeviceNet Trunk, Mini-Change
Region Europe
Type Single Ended
UPC 78678853165

Physical

Cable Diameter 12.10mm (.480")
Cable Length 3.0m (9.84')
Color - Cable Jacket Gray
Coupling Style Threaded
Gender Male-Pigtail
Keyway Single
LED Indicator No
Material - Cable Jacket PVC
Material - Connector Body PVC
Material - Coupling Nut Die-Cast Zinc
Material - Plating Mating Gold
Net Weight 252.910/g
Orientation Straight to Pigtail
Poles 5
Temperature Range - Operating -20°C to +80°C
Wire Size AWG 15, 18
Wire/Cable Type Thick Flex-Rated Cable

Electrical


Current - Maximum per Contact 4.0A
Voltage - Maximum 300V AC/DC

Material Info

Engineering Number DNF01A-M030

Reference - Drawing Numbers

Sales Drawing SD-130024-012



EU ELV

Not Reviewed

EU RoHS

**Compliant with
Exemption 6(c)**

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS	Not Relevant
ELV	Not Reviewed
RoHS Phthalates	Not Contained

Search Parts in this Series

[130024](#) Series