

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1302430003](#)
Status: **Active**
Overview: [Wide-Area Lighting Products](#)
Description: Haztex Hazardous and Wet Location Work Light 55W Twin Fluorescent with 12/3 SOOW Feed Thru 0.91m (3.0')

Documents:

[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Portable Lighting
Series	130243
Comments	Class 1, Division 2, Groups B, C, and D, Class 1, Division 2, Groups B, C, and D
NEMA Configuration	N/A
NEMA Rating	NEMA 3R
Outlet	Feed-Through
Overview	Wide-Area Lighting Products
Product Name	Haztex
Type	Wide Area Lamps
UPC	78172505864

Physical

Cord Length - Primary	0.91m (3.0')
Cord Length - Secondary	0.91m (3.0')
Depth	176.90m (6.960")
Duty	Hazardous
Guard Included	No
Guard Type	N/A
Height	166.50mm (6.555")
Length	706.37mm (27.810")
Material - Globe	Clear Polycarbonate
Material - Guard	Silicone Rubber
Mounting Style	Variable
Net Weight	8273.524/g
Packaging Type	Carton
Socket Construction	N/A

Electrical

Bulb Type	Fluorescent
Cord Type - Primary	12/3 SOOW
Lamp Type	PL-L 55/841/B
Lamp Wattage - Maximum	55W
Lumens	4800
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ

Material Info

Engineering Number	1075HZ2003123F003
--------------------	-------------------



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130243](#) Series