




FEATURES:

- Allows temperature probes with “K” type Mini-Connectors to be used with Digital Multimeters designed with a temperature measurement function from the Banana Jack input.

MATERIALS:

Insulator – Glass filled thermoplastic, color gray

Banana Plugs – Nickel plated, Beryllium Copper springs on a brass body

RATINGS:

Measurement Range – 0 to 220°F. (-18 to 104°C.)

ORDERING INFORMATION: Model 6369

Note: For use in low voltage environments. Do not exceed 30VAC/60VDC.

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm), .xxx = $\pm .005$ " (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA