









(2.54 mm) .100" PITCH • DISCRETE WIRE CABLE & COMPONENTS

SERIES	PINS PER ROW	WIRE GAUGE	PLATING OPTION	ASSEMBLY LENGTH	END OPTION	K	LATCH OPTION
MMSD = Double Row PVC Cable	-02, -03, -04, -05, -06, -08, -10, -12, -15, -16, -20, -25 (Standard sizes)	-20 -20C = Color Coded Cable (MMSD & MMSS only)	-L = 10 μ" (0.25 μm) Gold on contact, Tin on tail	-"XX.XX" = Assembly Length in Inches (82.55 mm) 03.25" min.	-S = Single Ended	-K = Keyed Polarization	(Metal latches for more rugged environments; -02, -05 & -10 positions only)
MMSDT = Double Row Blue *Teflon® Cable (20, 24, 28, 30 AWG only)		-22, -24 -24C = Color Coded Cable (MMSD & MMSS only)			-D = Double Ended (Latch Required)		-M = Single Ended, Metal Latches (Leave blank for plastic)
MMSS = Single Row PVC Cable		-26, -28 -28C = Color Coded Cable (MMSD & MMSS only)					Double Ended (-D) Crossed requires MMSD/MMSDT
MMSST = Single Row Blue *Teflon® Cable (20, 24, 28, 30 AWG only)		-30					-LUS = Plastic Latch up, straight
MMSD, MMSDT, MMSS, MMSST Board Mates: IPL1 (Does not mate with IPT1)				 Assembly Length ± (3.18) .125			
Cable Mates: MMTD(T), MMTS(T)							
* Dupont™ Teflon® is a registered trademark of E.I. du Pont de Nemours and Company or its affiliates.							
Teflon® cable is intended for crimp only. Contact Samtec for solderable cable applications.							




-20C, -24C, -28C CABLE COLOR CODING	
PIN	COLOR
1	BROWN
2	RED
3	ORANGE
4	YELLOW
5	GREEN
6	BLUE
7	VIOLET
8	GRAY
9	WHITE
10	BLACK
ETC	REPEAT

IPD1	POSITIONS PER ROW	ROW OPTION	K	LATCH OPTION
	-02, -03, -04, -05, -06, -08, -10, -12, -15, -16, -20, -25 (Standard sizes)	-S = Single Row	-K = Keyed Polarization	-M = Metal Latch (Metal for more rugged environments) (-02, -05 & -10 positions only) (Leave blank for plastic latch)
		-D = Double Row		



SERIES	WIRE GAUGE	01	PLATING OPTION
CC79L = Contact, Loose	-2630 = 26 to 30 AWG		-L = 10 μ " (0.25 μ m) Gold on contact, Tin on tail
CC79R = Contact, Full Reel (12,000 Parts per Reel)	-2024 = 20 to 24 AWG		



TOOLING

Hand Tool: CAT-HT-179-2030-13 (20-30 AWG)

Mini Applicator: CAT-MC-179-2024-XX-01 (20-24 AWG)

Mini Applicator: CAT-MC-179-2630 XX-01 (26-30 AWG)

Extraction Tool: CAT-EX-179-01

Not:
Some lengths, styles and
options are non-standard,
non-returnable.