



FMA8012BS-M

80X80X16

0.60~1.028 M³/MIN

MATERIAL

Frame	Plastic PBT 94V0
Impeller	Plastic PBT 94V0
Lead Wire	AWG26" "+" Red "-" Black
	Standard UL 1007
Option	Signal output
Bearing	Sleeve Bearing
Dimensions in mm	



Model	FMA8012BS-M
Rated Voltage DCV	12
Operating Voltage DCV	6.0-13.8
Rated Input W	1.44
Rated Current A	0.12
Operating Temperature °C	-10~70
Storage Temperature °C	-40~70
Speed RPM	2500
Max, Air Flow M ³ /Min(CFM)	0.7156(25.23)
Max, Air Pressure mmH2O	2.23
Noise DB	31.5
Bearing	
Weight (g)	APPROX.76

: Sleevebearing