

D

C

B






A

D

C


B

A



A-A

- △ 面より2mmの範囲で測定
2. 適用プリント基板厚 : 1.6mm
3. かん合相手ハウジング型番 : 174047
4. 推奨取付けネジ : JIS B1115, B1122 タッピンねじ、なべ2種
呼び径3、長さ7mm以上 (締付トルク : 0.39N-m以下)
- △ TO BE MEASURED WITHIN 2mm FROM
- 2 APPLICABLE P.C. BOARD THICKNESS: 1.6mm
- 3 THE MATING PLUG HOUSING PART NUMBER: 174047
- 4 RECOMMENDED MOUNTING SCREW: 3mmDIA, 7mmLENGTH(MIN.)
PAN HEAD, CLASS 2 TAPPING SCREW SPECIFIED IN JIS B1115,
B1122 (TIGHTENING TORQUE: 0.39N-m MAX.)



OBSOLETE	SELECTIVE-TIN (MATTE)		SELECTIVE GOLD	BLACK	1-5174055-2
	TIN-LEAD		SELECTIVE GOLD	BLUE	1-174055-5
	TIN-LEAD		SELECTIVE GOLD	BLACK	1-174055-2
	PRE-TIN			YELLOW	174055-7
OBSOLETE	PRE-TIN			BLUE	174055-5
	PRE-TIN			GREEN	174055-4
	SELECTIVE-TIN (MATTE)	SELECTIVE-TIN (BRIGHT)	BLACK	174055-3	
	PRE-TIN		BLACK	174055-2	
OBSOLETE	SELECTIVE-TIN		PRE-TIN	BLACK	174055-1
	SOLDERING SIDE 半田付け部		CONTACT SIDE 接触部側	COLOR 色	PART NUMBER 製品型番
CONTACT FINISH コンタクト仕上					

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
単位: 純
mm

MATERIAL
材料

HOUSING ; PBT
CONTACT ; BRASS

TOLERANCES UNLESS OTHERWISE SPECIFIED
一般公差

0 PLC	±
1 PLC	± -
2 PLC	± -
3 PLC	± -
4 PLC	± -
ANGLES	± -

FINISH
仕上

SEE TABLE

一般公差
(GENERAL TOLERANCE)

10以下	±0.2
10を越え 30以下	±0.25
30を越え 100以下	±0.3
100を越え	±0.4
角度	±3°

DWN
T.SHINOHARA
15FEB05

CHK
K.BETSUI
15FEB05

APVD
K.BETSUI
15FEB05

PRODUCT SPEC
製品規格

APPLICATION SPEC
取付適用規格

WEIGHT
6.1 g

CUSTOMER DRAWING

TE Connectivity

040 SERIES MULTI-LOCK I/O CONN.
20POSITION CAP ASSY
(HORIZONTAL TYPE)

SIZE
A2

CAGE CODE
00779

DRAWING NO
番号
C=174055

RESTRICTED TO
—

SCALE
尺度 2:1

SHEET
1 of 1

REV
G6