



LACING TAPES

NYLON Lacing Tape TYPE I Meets or exceeds MIL-T-43435B A-A-52080 Flat braid. Colors: Natural[N] or Black[0] Temperature -55°C to 121°C Available with a variety of finishes. See chart below.	RDS P/N	MIL SPEC SIZE	Strength (Min.)	Width	Thickness (Nom.)	Standard Spool
	LC43435-T1S1**	1	135 LB	.200"	.016"	250 yds
	LC43435-T1S2**	2	80 LB	.110"	.015"	250 yds
	LC43435-T1S3**	3	50 LB	.085"	.014"	500 yds
	LC43435-T1S4**	4	25 LB	.060"	.012"	500 yds
	LC43435-T1S5**	5	15 LB	.050"	.010"	500yds
POLYESTER Lacing Tape TYPE II Meets or exceeds MIL-T-43435B A-A-52081 Flat braid. Colors: Natural[N] or Black[0] Temperature -73°C to 177°C Available with a variety of finishes. See chart below.	LC43435-T2S1**	1	135 LB	.200"	.016"	250 yds
	LC43435-T2S2**	2	80 LB	.110"	.015"	250 yds
	LC43435-T2S3**	3	50 LB	.085"	.014"	500 yds
	LC43435-T2S4**	4	25 LB	.060"	.012"	500 yds
	LC43435-T2S5**	5	15 LB	.050"	.010"	500yds
TEFLON Lacing Tape TYPE III Meets or exceeds MIL-T-43435B A-A-52082 Flat braid. Color: Natural[N] (Brown) Temperature -73°C to 232°C Available with a variety of finishes. See chart below.	LC43435-T3S2**	2	30 LB	.120"	.011"	250 yds
	LC43435-T3S4**	4	15 LB	.065"	.011"	500 yds
	LC43435-T3S5**	5	10 LB	.025"	.011"	500yds
GLASS Lacing Tape TYPE IV Meets or exceeds MIL-T-43435B A-A-52083 Flat braid. Color: Natural[N] Temperature Stable to 800°F (427°C) Available with a variety of finishes. See chart below.	LC43435-T4S1**	1	200 LB	.225"	.016"	250 yds
	LC43435-T4S2**	2	100 LB	.110"	.016"	250 yds
	LC43435-T4S3**	3	75 LB	.085"	.016"	500 yds
	LC43435-T4S4**	4	50 LB	.060"	.016"	500 yds
	LC43435-T4S5**	5	--	.050"	.016"	500yds
NOMEX Lacing Tape TYPE V Meets or exceeds MIL-T-43435B A-A-52084 Flat braid. Color: Natural[N] With tracers for High Temp. identification Temperature -55°C to 260°C Available with a variety of finishes. See chart below.	LC43435-T5S1**	1	85 LB	.200"	.016"	250 yds
	LC43435-T5S2**	2	50 LB	.110"	.014"	250 yds
	LC43435-T5S3**	3	35 LB	.075"	.012"	500 yds
	LC43435-T5S4**	4	25 LB	.055"	.010"	500 yds
	LC43435-T5S5**	N/A	15 LB	.045"	.010"	500yds

Mil Spec Designation	Finish Type
A	No Finish
B	Wax
C	Synthetic Rubber, or Elastomer
D	Teflon
E	Vinyl
F	Silicone resin
G	Liquid Nylon
*	Self-Extinguishing (Meets requirements of Finish C)

Ordering Information:

RDS Part Number:

LC434-35-T1-S4 FB N

T1= Type I (Nylon)

S4= Size 4

FB= Finish B (Wax)

N = Color Natural (**0** for color Black)