





|  |   |   |   |   |   |   |   |  |
|--|---|---|---|---|---|---|---|--|
|  | 1 | 2 | 3 | 4 | 5 | 6 | 7 |  |
|--|---|---|---|---|---|---|---|--|

Male



Cover

- Product Specification
- Material
- Insulator : Glass-Filled Thermoplastic PBT, UL94V-0,Black
- Contact : Copper alloy, plating gold flash selective gold
- Shell : Steel, 1000µ" Tin Over 500µ" min Copper
- Electrical
- Contact Resistance : 20 milliohms Max at 1 AMP DC.
- Insulation Resistance : 1000 megohms at 500 VDC
- Dielectric Withstanding Voltage : 1000 VAC/rms 60Hz for 1 minute
- Current Rating : 3 AMP
- Voltage Rating : 250 VAC/rms 60Hz
- Wire Spec : 26 AWG-28 AWG
- Operating Temperature:-20°C--+85°C
- ⑤ UL E No #E198287

Order Code:

A-DXF xx LP111/Z

Contact style: F - Female S - Male

No. of Contacts 09 / 15 / 25 / 37


Standard: Quality class III

Without Insulator Support

Dimensions

| Positions | A     | B     | C     | E     | F     |
|-----------|-------|-------|-------|-------|-------|
| 9         | 30.81 | 24.99 | 16.92 | 11.08 | 13.10 |
| 15        | 39.20 | 33.30 | 25.25 | 19.39 | 20.70 |
| 25        | 53.04 | 47.04 | 38.96 | 33.24 | 33.68 |
| 37        | 69.40 | 63.50 | 55.42 | 49.86 | 50.30 |

Strain Relief



RoHS compliant

Unit:mm

| Scale     | Free  | ⑤   | Correct the UL-File number            | 03.04.2014 | Winnie |          | Date       | Name   | Customer-No.     |
|-----------|-------|-----|---------------------------------------|------------|--------|----------|------------|--------|------------------|
| TOLERANCE |       | ④   | Update 17.58&17.28 into 17.40&17.10mm | 07.03.2014 | Winnie | Drawn    | 15.08.2012 | Lucas  |                  |
| X.        | ±0.38 | ③   | Update the wire specification         | 28.06.2013 | Winnie | Approved | 03.04.2014 | Winnie | ASSMANN WSW-No.  |
| X.X       | ±0.25 | ②   | Add the wire specification            | 06.03.2013 | Winnie |          |            |        | A-DXF xx LP111/Z |
| X.XX      | ±0.13 | ①   | Add the UL file No.                   | 18.10.2012 | Winnie |          |            |        | Drawing-No.      |
| DIM       | TOL   | ①   |                                       |            |        |          |            |        | ASS 4891 CO      |
| X.°       | ±3°   |     |                                       |            |        |          |            |        | rev05            |
| X.X°      | ±1.0° | ①   | Drawn                                 | 15.08.2012 | Lucas  |          |            |        | Replace          |
| Angle     | TOL   | Id. | Modification                          | Date       | Name   |          |            |        | Sheet 1/2        |



ASS 4891 CO

rev05

|   |   |   |   |   |   |   |  |
|---|---|---|---|---|---|---|--|
| 1 | 2 | 3 | 4 | 5 | 6 | 7 |  |
|---|---|---|---|---|---|---|--|

