


(2,54 mm) .100"



BBS, BBL, BHS, BBD, BDL SERIES

# MACHINED BOARD STACKING STRIPS

**Mates with:**  
SS, SD, HSS, SL, SDL,  
ESS, ESD

## FEATURES

- Low profile design achieves (3,89 mm) .153" board spacings when mated with SL Series.
- Approach the reliability of a permanent connection with the flexibility of a separable connection.

## SPECIFICATIONS

For complete specifications see [www.samtec.com?BBS](http://www.samtec.com?BBS), [www.samtec.com?BBL](http://www.samtec.com?BBL), [www.samtec.com?BHS](http://www.samtec.com?BHS), [www.samtec.com?BBD](http://www.samtec.com?BBD) or [www.samtec.com?BDL](http://www.samtec.com?BDL)

### Insulator Material:

Black Glass Filled Polyester (BBS, BBD, BBL)

Black High Temp Nylon (BDL)

Black Liquid Crystal Polymer (BHS)

**Temperature Range:**  
-55°C to +125°C

**Terminal Material:**  
Phosphor Bronze or Brass

### Plating:

Au or Sn over 50µ" (1,27 µm) Ni

### RoHS Compliant:

Yes

### Lead-Free Solderable:

Wave only (BBS, BBD, BBL, BDL)


Wave, or reflow with all Au (BHS)

## RECOGNITIONS

For complete scope of recognitions see [www.samtec.com/quality](http://www.samtec.com/quality)



**Note:** Some lengths, styles and options are non-standard, non-returnable.



Due to technical progress, all designs, specifications and components are subject to change without notice.

[WWW.SAMTEC.COM](http://WWW.SAMTEC.COM)