

Crimping pliers - CRIMPFOX 50R - 1212041


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Crimping pliers, for ferrules without insulating collar according to DIN 46228 Part 1 and ferrules with insulating collar according to DIN 46228 Part 4, 35 mm² ... 50 mm², lateral entry, WM crimp

Why buy this product

- ✓ Ergonomically designed handles ensure an optimum grip and reduce the amount of force required by 25%



Key Commercial Data

Packing unit	1 STK
GTIN	 4 046356 453912
GTIN	4046356453912

Technical data

Dimensions

Length (b)	256 mm
Width (a)	25 mm
Height	68 mm

General

Color	black
Compression	WM crimp
Type of contact	Insulated and uninsulated ferrules
Designation	Crimping position 1
Max. cross section	35 mm²
AWG min	2
AWG max	1
Designation	Crimping position 2
Max. cross section	50 mm²
AWG max	1

Crimping pliers - CRIMPFOX 50R - 1212041

Technical data

General

Designation	Crimping position 3
Die station	Crimping position 4
	Crimping position 5
Weight	578 g
Min. cross section	35 mm ²
Max. cross section	50 mm ²

Approvals

Approvals

Approvals

EAC / EAC

Ex Approvals

Approval details

EAC		EAC-Zulassung
-----	---	---------------

EAC		C-DE.A*77.B.00766
-----	---	-------------------

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>