





- 1 HOUSING: NYLON, UL 94V-0 RATED, BLACK.
- 2 CONTACTS & RECEPTACLE SHIELD: 2.54 μ m [.000100] MIN TIN OVER 1.27 μ m [.000050] MIN NICKEL.
- 3 CONTACTS & RECEPTACLE SHIELD: BRASS.



5212045-1

PART
NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L. VARELA - 11-12-04 CHK C. ROHDE 11-12-04 APVD M. WALMSLEY 11-12-04	tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC 108-10047	NAME RECEPTACLE ASSY, RIGHT ANGLE, SHIELDED, 6 POSITION, CIRCULAR DIN	
	0 PLC $\pm$ - 1 PLC $\pm$ - 2 PLC $\pm$ 0.13 [.005] 3 PLC $\pm$ - 4 PLC $\pm$ - ANGLES $\pm$ 0° 30'	APPLICATION SPEC 114-40025	SIZE A2	CAGE CODE 00779
MATERIAL 1 3	FINISH 2	WEIGHT -	DRAWING NO C=5212045	RESTRICTED TO -
CUSTOMER DRAWING			SCALE 4:1	SHEET 1 of 1
			REV 01	