


SEVEN SEGMENT DISPLAY – 12.7 mm (0.5 INCH), Dual

DATA SHEET 3543 REV.1.2



Notes: All dimensions are in mm, tolerance is ± 0.25 mm (0.01") unless otherwise specified

Absolute Maximum Ratings $T_a=25^\circ\text{C}$

Parameter	Green	Unit
Power dissipation per segment	60	mw
Peak forward current per segment*	80	mA
Continuous forward current per segment	15	mA
Reverse voltage per segment	5	V
Operating temperature range	-35~85	$^\circ\text{C}$
Storage temperature range	-35~85	$^\circ\text{C}$
Solder temperature 1/16 inch below seating plane for 3 seconds at 260°C		

* 1/10 duty cycle 10 ms pulse width

Electro-optical Characteristic: ($T_a=25^\circ\text{C}$)

Part No.		Chip Material	Color	Wavelength (nm)	Iv (mcd) Typ. 20mA	Note
Common Anode	Common Cathode					
LN2005-G-AG	LN2005-G-CG	GaP	Green	572	13	
LN2005-RS-AGL	LN2005-RS-CGL	GaAlAs	Red	660	40	

Features

- 0.50 inch digit height, Gray surface
- Uniformly illuminated segments
- Wide viewing angle
- Easy mounting on PCB or socket

Description

LN2005 series display is fully compatible with industry standard 0.50" package with options of low current (-xxL), common anode (-Axx) and common cathode (-Cxx).