


REIKU-Kabelschutz-Wellrohre

REIKU Tubings for Cable Protection



PA	Polyamid	polyamide
TP	thermopl. Polyesterester	thermopl. polyesterester
R	Wellrohr	corrugated tubing
R	Roboter-Version	robot
F	Fahrzeug-Version	vehicle version
I	Isolier-Version	insulation version
B	schwarz	black
G	grau	grey
	Nennweite	Nominal width
F	Feinprofil	fine profile
G	Grobprofil	broad profile

PA R R G / PA R R B Polyamid 12, für Roboter/polyamide 12, for robots

Bestell-Nr./Article no grau/grey	schwarz/black	NW mm	für/for M/PG	d2	d1	Radius mm (stat.) (dyn.)	kg/100 m	(VE) m (PU) m
PA R R G-07G	PA R R B-07G	07	10/07	10,0	6,4	15 40	2,20	100
PA R R G-10F	PA R R B-10F	10	12/09	13,0	9,4	20 50	2,60	50
PA R R G-12F	PA R R B-12F	12	16/11	15,8	11,8	25 65	3,50	50
PA R R G-17F	PA R R B-17F	17	25/16	21,2	16,5	30 80	5,50	50
PA R R G-23F	PA R R B-23F	23	32/21	28,5	22,6	35 90	9,20	50
PA R R G-23G	PA R R B-23G	23	32/21	28,5	21,7	40 100	9,20	50
PA R R G-29F	PA R R B-29F	29	40/29	34,5	27,5	45 120	12,00	50
PA R R G-29G	PA R R B-29G	29	40/29	34,5	27,5	50 120	12,00	50
PA R R G-36G	PA R R B-36G	36	50/36	42,5	35,9	60 180	16,00	30
PA R R G-48G	PA R R B-48G	48	63/48	54,5	46,5	70 200	22,00	30
PA R R G-52G	PA R R B-52G	52		63,0	52,0	125 300	36,50	10/30
PA R R G-70G	PA R R B-70G	70		82,5	70,0	150 350	51,00	10/30
PA R R G-95G	PA R R B-95G	90		106,0	87,5	170 400	75,00	10/30

PA R F B Polyamid 12, verstärkt, schwarz/polyamide 12, strengthened, black

UL 105 °C

grau auf Anfrage/grey on request			UL recognized File E 168970 (M) 105°C ab Nennweite 17/from NW 17 onwards					
Bestell-Nr./Article no	NW mm	für/for M/PG	d2	d1	Radius mm (stat.) (dyn.)		kg/100 m	(VE) m (PU) m
PA R F B-10 F	10	10/09	13,0	9,4	25	60	3,10	50
PA R F B-12 F	12	12/11	15,8	11,6	30	80	4,50	50
PA R F B-17 G	17	25/16	21,2	14,8	50	100	8,10	50
PA R F B-23 G	23	32/21	28,2	21,2	60	110	11,70	50
PA R F B-29 G	29	40/29	34,5	27,5	75	160	17,10	50
PA R F B-36 G	36	50/36	42,0	34,4	110	250	18,90	30
PA R F B-48 G	48	63/48	54,0	46,1	170	300	26,60	30
PA R F B-52 G	52		62,0	52,0			41,00	10/30
PA R F B-70 G	70						60,00	10/30

PA R A B Polyamid 12, schwarz/polyamide 12, black

Bestell-Nr./Article no	NW mm	für/for M/PG	d2	d1	Radius mm (stat.) (dyn.)	kg/100 m	(VE) m (PU) m
PA R A B-10F	10	10/09	13,0	9,4	20 50	2,60	50
PA R A B-12F	12	12/11	15,5	11,8	25 65	3,50	50
PA R A B-17F	17	25/16	21,0	16,5	30 80	5,50	50
PA R A B-23G	23	32/21	28,0	22,3	40 100	9,20	50
PA R A B-29G	29	40/29	34,0	28,2	50 120	12,00	50
PA R A B-36G	36	50/36	42,0	35,9	60 180	16,00	30
PA R A B-48G	48	63/48	54,0	46,5	70 200	22,00	30
PA R A B-52G	52		62,8	52,0	125 300	36,50	10/30
PA R A B-70G	70		82,0	70,0	150 (350)	51,00	10/30