

Sales Outline Drawing**Revision A****Specifications:**

Resonant Frequency (Hz)	400 ± 100
Operating Voltage (Vdc)	20 ~ 28
Rated Voltage (Vdc)	24
Current Consumption Max. (mA)	35 at Rated Voltage
Sound Pressure Level Min. (dB)	85 at 10cm at Rated Voltage
Tone/Pulse Rate	Constant
Operating Temperature (°C)	-20 ~ +70
Storage Temperature (°C)	-30 ~ +80
Housing	ABS 707 UL94HB plastic resin (Color: Black)
Leading Wire	26 AWG
Weight (Grams)	8.2
Options	For other options contact factory

RoHS Compliant**Dimensions:** (units: mm)