


Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriete de c FCI. Droits de reproduction FCI.




All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.




Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriete de c FCI. Droits de reproduction FCI.




All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.




SINGLE PORT
SCALE 3:2




DUAL PORT
SCALE 3:2



TRIPLE PORT
SCALE 3:2



QUAD PORT
SCALE 3:2




title	BULKHEAD STYLE (MOD.)	dwg no	98275	Rev.
	ASSEMBLY w/MNTG. BRACKET			E
catalog no	CUSTOMER		sheet 2 of 4	


Tous droits strictement réservés. Reproduction ou communication à des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.



RECOMMENDED PCB FOOTPRINT AS VIEWED FROM COMPONENT SIDE



RECOMMENDED BULKHEAD OPENING

title	BULKHEAD STYLE (MOD.)		dwg no	98275		Rev. E
	ASSEMBLY w/MNTG. BRACKET					
catalog no			CUSTOMER		sheet 3 of 4	

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriete de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NUMBER	TYPE OF ASSY.	CONTACT PLATING	HOUSING COLOR	NO. of PORTS	PACKAGE
98275-001	BULKHEAD ASS'Y.	15GXT	BLACK	1	TRAY
98275-0011	BULKHEAD ASS'Y.	15GXT	BLACK	1	TRAY
98275-001B	BULKHEAD ASS'Y.	15GXT	BLACK	1	TRAY
98275-002	BULKHEAD ASS'Y.	30Au	NATURAL	1	TRAY
98275-003	BULKHEAD ASS'Y.	15GXT	BLACK	1	TAPE & REEL
98275-004	BULKHEAD ASS'Y.	30Au	NATURAL	1	TAPE & REEL
98275-005	BULKHEAD ASS'Y.	15GXT	BLACK	2	TRAY
98275-006	BULKHEAD ASS'Y.	30Au	NATURAL	2	TRAY
98275-007	BULKHEAD ASS'Y.	15GXT	BLACK	3	TRAY
98275-008	BULKHEAD ASS'Y.	30Au	NATURAL	3	TRAY
98275-009	BULKHEAD ASS'Y.	15GXT	BLACK	4	TRAY
98275-010	BULKHEAD ASS'Y.	30Au	NATURAL	4	TRAY

- NOTES:
1. UNLESS OTHERWISE SPECIFIED:
DIMENSIONS AND TOLERANCES ARE IN ACCORDANCE WITH ASME Y14.5M, 1994.
ALL UNTOLERANCED DIMENSIONS ARE BASIC.

⌀

0.127
2. DIMENSIONS SHOWN IN PARANTHESES ARE "REF. DIMS" AS PER ASME Y14.5M, 1994.
3. FOR DETAILS OF PCI BRACKET SEE DRAWING 73592.
- ④ DATUMS & DIMENSIONS ESTABLISHED BY CUSTOMER.
5. CONNECTOR WILL ACCOMMODATE P.C.B'S. UP TO 3.00 MAX THICKNESS
- ⑥ MATERIAL: CONTACTS: BeCu
SHIELD: PHOS BRONZE
HOUSING: UL 94 V-0 RATED HIGH TEMP. THERMOPLASTIC
BRACKET: A91 MAGNESIUM OR ZAMAK3
PLATING: CONTACTS: NOBLE METAL PLATING IN CONTACT AREA
SHIELD: TIN-LEAD
BRACKET: ELECTROLESS TIN-LEAD
7. RECOMMENDED PCI BRACKET OR PANEL THICKNESS OF 0.76±0.03.
- ⑧ MOUNTING BRACKET IS TO BE SOLDERED TO CONNECTOR SHIELD ALONG THE TOP IN THE AREA SHOWN, WITH EXECPTION TO ITEM -001B THAT WILL INCLUDE SOLDER ALONG BOTH SIDES OF THE TOP FLANGE.

title	BULKHEAD STYLE (MOD.)		dwg no	98275		Rev. E
	ASSEMBLY w/MNTG. BRACKET					
catalog no			CUSTOMER		sheet 4 of 4	