

Miniature Fuse, 6.3 x 32 mm, Super-Time-Lag TT, NNO, 220 VAC



220 VAC · Super-Time-Lag TT



NNO

Description

- Low Breaking Capacity

References

We recommend for new applications the type 172600
Last order date: 31.12.2013


Weblinks

[pdf-datasheet](#), [html-datasheet](#), [General Product Information](#), [Approvals](#), [CE declaration of conformity](#), [RoHS](#), [CHINA-RoHS](#), [REACH](#), [e-Shop](#), [SCHURTER-Stock-Check](#), [Distributor-Stock-Check](#), [Detailed request for product](#)

Technical Data

Rated Voltage	32 - 220 VAC
Rated current	1.6 - 30 A
Breaking Capacity	100 A
Characteristic	Super-Time-Lag TT
Mounting	Fuseholder / Clip
Admissible Ambient Air Temp.	-40 °C to 85 °C
Climatic Category	40/085/56 acc. to IEC 60068-1
Material: Tube	Glass
Unit Weight	1.5 g
Storage Conditions	0 °C to 60 °C, max. 70% r.h.
Product Marking	TD3AG, Current, Characteristic


Dimension



Pre-Arcing Time

Rated Current In	1.1 x In min.	1.45 x In max.	2.0 x In min.	2.0 x In max.	3.0 x In min.	3.0 x In max.	5.0 x In min.	5.0 x In max.
1.6 A - 30 A	60 min	60 min	12 s	30 s	4 s	9 s	1 s	4 s

Time-Current-Curves



All Variants

Rated Current [A]	Rated Voltage [VAC]	Breaking Capacity	Voltage Drop 1.0 In typ. [mV]	Order Number
1.6	220	1)	620	7045.1110
2	220	1)	470	7045.1120
2.5	220	1)	470	7045.1130
3.15	220	1)	370	7045.1140
4	220	1)	290	7045.1150
8	220	1)	170	7045.1180
10	220	1)	180	7045.1190
12.5	220	1)	120	7045.1210
20	32	1)	80	7045.1310
25	32	1)	70	7045.1410
30	32	1)	40	7045.1420

Availability for all products can be searched real-time:<http://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER>

1) 100 A @ 220 VAC

Packaging Unit Small Box Pack (10 pcs.)