

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0022013057

Status:

Active

Overview:

KK®

Description:

2.54mm (.100") Pitch KK® Crimp Terminal Housing, Friction Ramp, 5 Circuits, Use with 2759|6459|41572

Documents:

3D Model

Drawing (PDF)

Product Specification PS-10-07 (PDF)


RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Housings
Series	2695
Overview	KK®
Product Name	KK®
Physical	
Circuits (maximum)	5
Color - Resin	Natural (White)
Flammability	94V-0
Gender	Female
Glow-Wire Compliant	No
Lock to Mating Part	Yes
Material - Resin	Nylon
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface (in)	0.100 In
Pitch - Mating Interface (mm)	2.54 mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	0°C to +75°C

Electrical	
CSA	LR19980
UL	E29179

Material Info	
Old Part Number	2695-05RP

Reference - Drawing Numbers	
Product Specification	PS-10-07
Sales Drawing	SD-2695



EU RoHS

ELV and RoHS Compliant

REACH SVHC

Contains SVHC: No

Halogen-Free

Status

Halogen-Free

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

2695Series

Mates With

2.54mm (.100") Pitch KK® Crimp Terminal Housing, Friction Ramp, 5 Circuits, Use with 2759|6459|41572

Use With

KK® Crimp Terminal Housing [2695](#) , [6471](#) , [7880](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION